



390-052 Self-Locking Rotatable Coupling Composite 45° RFI/EMI Environmental Backshell with Strain-Relief Clamp or Nut



Composite Backshells



Entry Code	Clamp Saddle Closed
10	.16 (4.1)
12	.29 (5.1)
14	.40 (10.2)
16	.52 (13.2)
18	.58 (14.7)
20	.64 (16.0)
22	.72 (18.3)
24	.79 (20.1)
28	.89 (22.0)
32	.96 (24.0)



Entry Code	H		J		Cable Range *	
	±.06	(1.5)	±.06	(1.5)	Minimum	Maximum
10	.94	(23.9)	.80	(20.3)	.13 (3.3)	.25 (6.4)
12	1.17	(29.7)	.93	(23.6)	.25 (6.4)	.38 (9.7)
14	1.28	(32.5)	1.06	(26.9)	.31 (7.9)	.44 (11.2)
16	1.41	(35.8)	1.22	(31.0)	.50 (12.7)	.63 (15.9)
18	1.50	(38.1)	1.24	(31.5)	.56 (14.2)	.69 (17.5)
20	1.56	(39.6)	1.37	(34.8)	.63 (16.0)	.75 (19.1)
22	1.69	(42.9)	1.49	(37.8)	.75 (19.1)	.88 (22.2)
24	1.81	(46.0)	1.62	(41.1)	.88 (22.4)	1.00 (25.4)
28	1.91	(48.5)	1.68	(42.7)	1.00 (25.4)	1.13 (28.6)

* Cable range equals diameter of cable outer jacket.

Shell Size For Connector Designator		K		L		Max Entry Dash No. *
A & F/L	H	±.06	(1.5)	±.06	(1.5)	
08	09	.72	(18.3)	.88	(22.4)	10
10	11	.75	(19.1)	.94	(23.9)	12
12	13	.75	(19.1)	1.00	(25.4)	14
14	15	.76	(19.3)	1.03	(26.2)	16
16	17	.78	(19.8)	1.06	(26.9)	20
18	19	.79	(20.1)	1.07	(27.2)	20
20	21	.82	(20.8)	1.09	(27.7)	22
22	23	.86	(21.8)	1.14	(29.0)	24
24	25	.92	(23.4)	1.17	(29.7)	28

* Consult factory for additional entry sizes available.

XM*	Electroless Nickel
XW*	Cadmium Olive
	Drab Over
	Electroless Nickel

* Note: Coupling nut supplied unplated.

Metric dimensions (mm) are in parentheses and are for reference only.