



**Note: See Table I and Page D-2 for Front-End Details and Shell Size References**



Entry Code	Entry Dia. ±.03 (0.8)	X Dia. ±.03 (0.8)
04	.25 (6.4)	.51 (13.0)
05	.31 (7.9)	.51 (13.0)
07	.44 (11.2)	.51 (13.0)
09	.56 (14.2)	.63 (16.0)
11	.68 (17.3)	.63 (16.0)
13	.81 (20.6)	.63 (16.0)
15	.94 (23.9)	.63 (16.0)
16	1.00 (25.4)	.63 (16.0)
17	1.16 (29.5)	.63 (16.0)
20	1.25 (31.8)	.63 (16.0)

Consult factory for shrink boot and/or O-Ring to be supplied with part.

Shell Size For Connector Designator*					E	F	G	Max Entry Dash No**
A	F/L	H	G	U	±.06 (1.5)	±.09 (2.3)	±.09 (2.3)	
08	08	09	—	—	.69 (17.5)	.88 (22.4)	1.36 (34.5)	04
10	10	11	—	08	.75 (19.1)	1.00 (25.4)	1.42 (36.1)	05
12	12	13	11	10	.81 (20.6)	1.13 (28.7)	1.48 (37.6)	07
14	14	15	13	12	.88 (22.4)	1.31 (33.3)	1.55 (39.4)	09
16	16	17	15	14	.94 (23.9)	1.38 (35.1)	1.61 (40.9)	11
18	18	19	17	16	.97 (24.6)	1.44 (36.6)	1.64 (41.7)	13
20	20	21	19	18	1.06 (26.9)	1.63 (41.4)	1.73 (43.9)	15
22	22	23	—	20	1.13 (28.7)	1.75 (44.5)	1.80 (45.7)	17
24	24	25	23	22	1.19 (30.2)	1.88 (47.8)	1.86 (47.2)	20

\*\*Consult factory for additional entry sizes available.

XM*	Electroless Nickel
XW*	Cadmium Olive Drab Over Electroless Nickel

\* Note: Coupling nut supplied unplated.

Metric dimensions (mm) are in parentheses and are for reference only.