


RECEPTACLE HOLDER

PLUG HOLDER



NO POLARIZATION REQUIRED

TABLE I: CONNECTOR SHELL SIZE ORDER NUMBER

Shell Size	Max. Recommended Torque (Inch Pounds) Composite		A Dia. Max.	B Dia. Max.	C Dim. Max.
	Series I	Series II			
08	40	40	.478 (12.1)	.358 (9.1)	.910 (23.1)
10	40	40	.599 (15.2)	.486 (12.3)	.910 (23.1)
12	40	40	.758 (19.3)	.598 (15.2)	.910 (23.1)
14	40	40	.882 (22.4)	.723 (18.4)	.910 (23.1)
16	40	40	1.007 (25.6)	.848 (21.5)	.910 (23.1)
18	40	40	1.133 (28.8)	.948 (24.1)	.910 (23.1)
20	80	80	1.257 (31.9)	1.073 (27.3)	.910 (23.1)
22	80	80	1.382 (35.1)	1.198 (30.4)	.910 (23.1)
24	80	80	1.507 (38.3)	1.323 (33.6)	.910 (23.1)

NOTES

- Also mates with MIL-C-83723, Series I; 40M39569.
- Metric dimensions (mm) are indicated in parentheses.
- Material: Case hardened carbon steel with electroless nickel finish.
- Receptacle and plug holder drives: 1/4" - Shell sizes 08, 10, 12; 3/8" - Shell sizes 14 and up.