




390-001 Submersible EMI/RFI Cable Sealing Backshell with Strain Relief Type A - Rotatable Coupling - Low Profile

CONNECTOR DESIGNATORS **A-F-H-L-S** ROTATABLE COUPLING

TYPE A OVERALL SHIELD TERMINATION




**STYLE 2
(STRAIGHT)**
See Note 1)




**STYLE 2
(45° & 90°)**
See Note 1)


-445 Now Available with the "NESTOR"
Glenair's Non-Detent, Spring-Loaded, Self-Locking Coupling.
Add "-445" to Specify This AS85049 Style "N" Coupling Interface.




**STYLE H
Heavy Duty**
(Table X)



**STYLE A
Medium Duty**
(Table XI)



**STYLE M
Medium Duty**
(Table XI)



**STYLE D
Medium Duty**
(Table XI)

