



**600H005**  
**Plug and Receptacle Holder**  
**MIL-C-38999 Series III**



**TABLE I: CONNECTOR SHELL SIZE ORDER NUMBER**

Shell Size	Com'l	Mil. Ref.	Max. Recommended Torque (Inch Pounds)	A Dia.		B Dia.		C Dim.	
				Composite	Max.	Max.	Max.		
09		A	40	.577	(14.7)	.438	(11.1)	1.031	(26.2)
11		B	40	.709	(18.0)	.566	(14.4)	1.031	(26.2)
13		C	40	.829	(21.1)	.678	(17.2)	1.031	(26.2)
15		D	40	.954	(24.2)	.803	(20.4)	1.031	(26.2)
17		E	40	1.107	(28.1)	.928	(23.6)	1.031	(26.2)
19		F	40	1.190	(30.2)	1.033	(26.2)	1.031	(26.2)
21		G	80	1.315	(33.4)	1.158	(29.4)	1.031	(26.2)
23		H	80	1.440	(36.6)	1.283	(32.6)	1.031	(26.2)
25		J	80	1.565	(39.8)	1.408	(35.8)	1.031	(26.2)

**NOTES**

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 09, 11 and 13; 3/8" - Shell sizes 15 and up.