



801-037 and 801-040
Series 801 Mighty Mouse High-Speed
Double-Start ACME Threads
Crimp Receptacle Connector Ordering Information










In-Line
Shell Style 01



Rear Panel Jam Nut Mount
Shell Style 07



Square Flange Mount
Shell Style 02

HOW TO ORDER					
Sample Part Number					
801-037	-02	Z1	6-4	S	A
Series	Shell Style	Shell Material / Finish	Shell Size- Insert Arrangement	Contact Type	Shell Key Position
 801-037 Receptacle with Banding Platform	 -01 In-Line For Free-Hanging Cables	M Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Cadmium with Olive Drab Chromate ZNU Aluminum / Zinc-Nickel with Black Chromate	 6 - 4	Connector supplied with contacts A Pin Connector, Less Contacts B Socket Connector, Less Contacts	A Normal Alternate Key Positions: B C D E F
 801-040 Receptacle with Accessory Thread	 -02 Square Flange For Front or Rear Mounting	MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant	 6 - 7  7 - 10	P Pin S Socket G Pin with 30 AWG Crimp Barrel H Socket with 30 AWG Crimp Barrel Connectors with contacts are supplied with signal crimp contacts. These contacts are not installed.	

Dimensions in Inches (millimeters) are subject to change without notice.