

**801-044 and 801-045 High Speed (SATA)
Overmolded Differential Pair Cordsets
Series 801 Mighty Mouse Double-Start ACME Thread**



Series 801
High Speed
Mighty Mouse

4 PAIR DIFFERENTIAL HIGH SPEED OVERMOLDED CORDSET

| Sample Part Number | | | | | | | | |
|--|--|---|---------------------|--|-------------|--|--------------------|--|
| 801-044 | -C | D | 8 | Z1 | 7-10 | P | A | -72 |
| Series | End A Connector | End B Connector | Wire Size | Shell Material / Finish | Insert Arr. | Protective Cover | Shell Key Pos. | Length |
| 801-044 Overmolded Cordset, with Size #23 Contacts | -A Plug, with Male Pin Contacts | A Plug, with Male Pin Contacts | 8 #28 AWG | M Aluminum / Electroless Nickel | 7-10 | P Metal Protective Covers Included | A Normal | Overall Length In Inches 12 Inch Min. |
| | -B Plug, with Female Socket Contacts | B Plug, with Female Socket Contacts | | NF Aluminum / Cadmium with Olive Drab Chromate | | | B Pos. B | |
| | -C Receptacle, with Male Pin Contacts | C Receptacle, with Male Pin Contacts | | ZNU Aluminum / Zinc-Nickel with Black Chromate | | | C Pos. C | |
| | -D Receptacle, with Female Socket Contacts | D Receptacle, with Female Socket Contacts | | MT Aluminum / Nickel-PTFE | | | D Pos. D | |
| | | N No Connector (Single-Ended) | | Z1 Stainless Steel / Passivated | | | E Pos. E | |
| | | | | | | N No Covers Supplied | F Pos. F | |

OVERMOLDED SATA CORDSET

| Sample Part Number | | | | | | | | |
|--|--|---|---------------------|--|-------------|--|--------------------|--|
| 801-045 | -B | N | 4 | NF | 6-7 | N | A | -48 |
| Series | End A Connector | End B Connector | Wire Size | Shell Material / Finish | Insert Arr. | Protective Cover | Shell Key Pos. | Length |
| 801-045 Overmolded Cordset, with Size #23 Contacts | -A Plug, with Male Pin Contacts | A Plug, with Male Pin Contacts | 4 #28 AWG | M Aluminum / Electroless Nickel | 6-7 | P Metal Protective Covers Included | A Normal | Overall Length In Inches 12 Inch Min. |
| | -B Plug, with Female Socket Contacts | B Plug, with Female Socket Contacts | | NF Aluminum / Cadmium with Olive Drab Chromate | | | B Pos. B | |
| | -C Receptacle, with Male Pin Contacts | C Receptacle, with Male Pin Contacts | | ZNU Aluminum / Zinc-Nickel with Black Chromate | | | C Pos. C | |
| | -D Receptacle, with Female Socket Contacts | D Receptacle, with Female Socket Contacts | | MT Aluminum / Nickel-PTFE | | | D Pos. D | |
| | | N No Connector (Single-Ended) | | Z1 Stainless Steel / Passivated | | | E Pos. E | |
| | | | | | | N No Covers Supplied | F Pos. F | |

Contact factory for wiring schematics