


# Cable Shield Grounding Assembly Male - GA/CSGA



Cable Shield  
Grounding  
Assemblies



**TABLE II**

Part Number	A Thread	Max Cable O.D.	Min Shield O.D.	B Max	Shrink Tube Part Number
GA/CSGA-A (SM)	7/8 - 12 UN	.250 (6.4)	.125 (3.2)	1.12 (28.4)	HRSR 125
GA/CSGA-A	7/8 - 12 UN	.406 (10.3)	.200 (5.1)	1.12 (28.4)	HRSR 125
GA/CSGA-B	1 - 12 UN	.515 (13.1)	.260 (6.6)	1.12 (28.4)	HRSR 125
GA/CSGA-C	1 1/8 - 12 UN	.640 (16.3)	.400 (10.2)	1.32 (33.5)	HRSR 175
GA/CSGA-D	1 1/4 - 12 UN	.750 (19.1)	.400 (10.2)	1.63 (41.4)	HRSR 175
GA/CSGA-E	1 1/4 - 12 UN	.812 (20.6)	.430 (10.9)	1.63 (41.4)	HRSR 175
GA/CSGA-F	1 5/16 - 12 UN	.843 (21.4)	.470 (11.9)	1.75 (44.5)	HRSR 200
GA/CSGA-G	1 1/2 - 12 UN	.953 (24.2)	.580 (14.7)	1.88 (47.8)	HRSR 200
GA/CSGA-J	1 5/8 - 12 UN	1.062 (27.0)	.690 (17.5)	1.88 (47.8)	HRSR 200
GA/CSGA-K	1 3/4 - 12 UN	1.172 (29.8)	.800 (20.3)	2.06 (52.3)	HRSR 250
GA/CSGA-L	1 13/16 - 12 UN	1.265 (32.1)	.890 (22.6)	2.18 (55.4)	HRSR 250
GA/CSGA-M	2 - 12 UN	1.406 (35.7)	1.010 (25.7)	2.32 (58.9)	HRSR 250
GA/CSGA-N	2 1/16 - 12 UN	1.515 (38.5)	1.130 (28.7)	2.38 (60.5)	HRSR 250
GA/CSGA-P	2 3/16 - 12 UN	1.625 (41.3)	1.200 (30.5)	2.44 (62.0)	HRSR 250
GA/CSGA-R	2 5/16 - 12 UN	1.750 (44.5)	1.250 (31.8)	2.75 (69.9)	HRSR 300
GA/CSGA-S	2 11/16 - 12 UN	1.875 (47.6)	1.380 (35.1)	2.88 (73.2)	HRSR 300
GA/CSGA-T	2 7/8 - 12 UN	2.062 (52.4)	1.560 (39.6)	3.13 (79.5)	HRSR 400
GA/CSGA-V	3 - 12 UN	2.187 (55.5)	1.690 (42.9)	3.25 (82.6)	HRSR 400

1. Metric dimensions (mm) are indicated in parentheses.

2. Material/Finish:

Adapters - Al Alloy/Cadmium Olive Drab Over Electroless Nickel (500 Hour Salt Spray).\*

Ferrule and Grounding Springs - Cres/Passivate.

Tubing - Heat Shrinkable, Flame Retardant, With Adhesive.

\*Available in Passivated 316 Stainless Steel, add 49A to end of part number.