






380-100 Self-Locking Rotatable Coupling Composite Straight and 90° RF/EMI Backshell with Qwik-Clamp



Note: See Table I and Page D-2 For Front-End Details and Shell Size References



US PATENT 5211576

TABLE II: CABLE ENTRY

Entry Code	H (Max)		J (Max)		Cable Range			
	Minimum	Maximum	Minimum	Maximum	Minimum	Maximum		
08	.72	(18.3)	.87	(22.1)	.10	(2.5)	.25	(6.4)
12	.91	(23.1)	1.01	(25.7)	.20	(5.1)	.38	(9.7)
16	1.09	(27.7)	1.11	(28.2)	.33	(8.4)	.50	(12.7)
20	1.22	(31.0)	1.11	(28.2)	.45	(11.4)	.63	(15.9)
24	1.34	(34.0)	1.11	(28.2)	.52	(13.2)	.75	(19.1)
28	1.53	(38.9)	1.26	(32.0)	.64	(16.3)	.88	(22.2)
32	1.72	(43.7)	1.41	(35.8)	.77	(19.6)	1.00	(25.4)
36	1.85	(47.0)	1.41	(35.8)	.86	(21.8)	1.13	(28.6)
40	1.97	(50.0)	1.41	(35.8)	.98	(24.9)	1.25	(31.8)
44	2.09	(53.1)	1.53	(38.9)	1.13	(28.6)	1.38	(34.9)

TABLE I: CONNECTOR SHELL SIZE

Shell Size For Connector Designator					E ±.06 (1.5)	F ±.09 (2.3)	G ±.09 (2.3)	Max Entry Dash No.**			
A	F/L	H	G	U							
08	08	09	-	-	.69	(17.5)	.88	(22.4)	1.06	(26.9)	08
10	10	11	-	08	.75	(19.1)	1.00	(25.4)	1.13	(28.7)	12
12	12	13	11	10	.81	(20.6)	1.13	(28.7)	1.19	(30.2)	16
14	14	15	13	12	.88	(22.4)	1.31	(33.3)	1.25	(31.8)	20
16	16	17	15	14	.94	(23.9)	1.38	(35.1)	1.31	(33.3)	24
18	18	19	17	16	.97	(24.6)	1.44	(36.6)	1.34	(34.0)	28
20	20	21	19	18	1.06	(26.9)	1.63	(41.4)	1.44	(36.6)	32
22	22	23	-	20	1.13	(28.7)	1.75	(44.5)	1.50	(38.1)	36
24	24	25	23	22	1.19	(30.2)	1.88	(47.8)	1.56	(39.6)	40
28	-	-	25	24	1.34	(34.0)	2.13	(54.1)	1.66	(42.2)	44

**Consult factory for additional entry sizes available.

TABLE III: FINISH

XM*	Electroless Nickel
XW*	Cadmium Olive Drab Over Electroless Nickel

* Note: Coupling nut & saddle bars supplied unplated.

Metric dimensions (mm) are in parentheses and are for reference only.