

TABLE I: INSERTION AND REMOVAL TOOLS PART NUMBERS, SIZE & DIMENSIONS

PART NUMBER	CONTACT SIZE	WIRE SIZE		INSERTION TOOL	REMOVAL TOOL
		mm ²	AWG	Commital P/N	Commital P/N
10-375-20	20	0,15-0,6	26-20	M.117346	M.118251
10-40579	18	0,15-0,6	26-20	M.117346	M.118249
10-40553	16S	1-1,5	18-16	M.117345	M.118250
10-40553-12	16S	0,6	20	M.117345	M.118250
10-40553-13	16S	0,15-0,6	26-20	M.117346	M.118250
10-40553-15	16S	0,75-1,0	18	M.117345	M.118250
10-40553-20	16S	1-2	14	M.117345	M.118250
10-40553-26	16S	3	12	M.117082	M.118250
10-40557	16	1-1,5	18-16	M.117345	M.118250
10-40557-08	16	0,15-0,2	26-24	M.117346	M.118250
10-40557-12	16	0,6	20	M.117345	M.118250
10-40557-13	16	0,15-0,6	26-20	M.117346	M.118250
10-40557-15	16	0,75-1,0	18	M.117345	M.118250
10-40557-20	16	1-2	14	M.117345	M.118250
10-40557-26	16	3	12	M.117082	M.118250
10-40557-32	16	/	32-28	M.117345	M.118250
10-40561	12	2,5-3,5	12	M.117082	M.118250
10-40561-12	12	0,6	20	M.117345	M.118250
10-40561-15	12	0,75-1,0	18	M.117082	M.118250
10-40561-20	12	1-2	18-14	M.117082	M.118250
10-40561-22	12	2,5	/	M.117082	M.118250
10-40561-30	12	4-5	/	M.117082	M.118250
10-40561-30M	12	4	/	M.117082	M.118250
10-40561-38	12	6	10	M.117082	M.118250
10-40561-50	12	10	/	M.117344	M.118260
10-40561-58	12	13,2	6	M.117344	M.118260
10-40792	8	9	8	M.117344	M.118260
10-40792-15	8	0,75-1,0	18	M.117082	M.118260

Please consult our sales department for other contact options or crimp tooling details.



Insertion Tool



Removal Tool

**ITS Bayonet Connector Assemblies
Pin Crimp Contacts
Insertion and Removal tools**



TABLE I: INSERTION AND REMOVAL TOOLS PART NUMBERS, SIZE & DIMENSIONS

PART NUMBER	CONTACT SIZE	WIRE SIZE		INSERTION TOOL	REMOVAL TOOL
		mm ²	AWG	Commital P/N	Commital P/N
10-40792-18	8	1-2	18-14	M.117082	M.118260
10-40792-20	8	2	14	M.117082	M.118260
10-40792-26	8	3	12 -14	M.117082	M.118260
10-40792-30	8	4-5	/	M.117082	M.118260
10-40792-38	8	6	10	M.117344	M.118260
10-40792-50	8	10	/	M.117344	M.118260
10-40792-58	8	13,2	6	M.117344	M.118260
10-113474-4P	4	22	4	M.117347	M.118270
10-113474-4P-22	4	2,5	/	M.117082	M.118270
10-113474-4P-25	4	25	/	M.117347	M.118270
10-113474-4P-26	4	3	/	M.117082	M.118270
10-113474-4P-30	4	4-5	/	M.117082	M.118270
10-113474-4P-38	4	6	10	M.117344	M.118270
10-113474-4P-50	4	10	/	M.117344	M.118270
10-113474-4P-62	4	16	/	M.117347	M.118270
10-113474-1P	0	50-60	0	M.117348	M.118280
10-113474-1P-107	0	50	/	M.117348	M.118280
10-113474-1P-25	0	25	/	M.117347	M.118280
10-113474-1P-35	0	35	/	M.117348	M.118280
10-113474-1P-45	0	9	8	M.117344	M.118280
10-113474-1P-50	0	10	/	M.117344	M.118280
10-113474-1P-62	0	16	/	M.117347	M.118280
10-113474-0P	4/0	107	4/0	/	/
10-113474-0P-78	4/0	25	/	/	/
10-113474-0P-107	4/0	50	/	/	/
10-113474-0P-135	4/0	67,4	2/0	/	/
10-113474-0P-144	4/0	70	/	/	/

Please consult our sales department for other contact options or crimp tooling details.



Insertion Tool



Removal Tool