

600G005
Plug and Receptacle Holder
MIL-C-28840





TABLE I: CONNECTOR SHELL SIZE ORDER NUMBER

Shell Size	Max. Recommended Torque (Inch Pounds) Composite	A Dia. Max.	B Dia. Max.	C Dim. Max.
11	40	.697 (17.7)	.502 (12.8)	.945 (24.0)
13	40	.822 (20.8)	.626 (15.9)	.945 (24.0)
15	40	.995 (25.3)	.798 (20.3)	.945 (24.0)
17	40	1.058 (26.9)	.868 (22.0)	.945 (24.0)
19	40	1.245 (31.6)	1.035 (26.3)	.945 (24.0)
23	80	1.433 (36.4)	1.220 (31.0)	.945 (24.0)
25	80	1.558 (39.6)	1.381 (35.1)	.945 (24.0)
29	80	1.745 (44.3)	1.547 (39.3)	.945 (24.0)
33	120	1.933 (49.1)	1.739 (44.2)	.945 (24.0)

NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 11 and 13; 3/8" - Shell sizes 15 and up.