


A

Receptacles


Plugs

Selected  
Shell Styles


**ITS 00**  
Front Panel Mount  
Square Flange  
Receptacle with  
Accessory Threads




**ITS 02**  
Front Panel Mount  
Square Flange Receptacle.  
No Accessory Thread




**ITS 01**  
In Line Cylindrical  
Receptacle with Accessory  
Thread




**ITS 030**  
Rear Panel Mount Square  
Flange Receptacle with  
Accessory Thread




**ITS 03**  
Rear Panel Mount Square  
Flange Receptacle. No  
Accessory Thread



**ITS 05**  
Dummy Plug Stowage  
Receptacle




**ITS 07**  
Rear Panel Mount Jam nut  
Receptacle. No Accessory  
Thread



**ITS 070**  
Rear Panel Mount Jam nut  
Receptacle with Accessory  
Thread



**ITS PP**  
Through Bulkhead Square  
Flange Receptacle.



**26**  
Panel Mounting  
Plug



**06**  
Standard Coupling  
Nut




**06 GG**  
Rubber Covered  
Coupling Nut




**A/R**  
Standard  
Backshell



**PG/M**  
Metric Thread  
Straight Adapter




**N2N5**  
Long Backshell with  
Cable Clamp Type "C"




**N8**  
Long Backshell with  
Cable Clamp Type "A"



**RS**  
Lipped Backshell



**GR**  
Backshell with Rotating  
Coupling Nut Shrink Boot  
Adapter




**PHM**  
Environmental Cable  
Clamp

**PHM-EMI**  
EMI/RFI  
Environmental Cable  
Clamp

# Glenair Series ITS

## MIL-DTL-5015 Type Reverse Bayonet Connectors

### Summary of Connector Styles and Backshells



#### Backshells and Accessories

#### Adapters and Cable Clamps

