



NO POLARIZATION REQUIRED

TABLE I: CONNECTOR SHELL SIZE ORDER NUMBER

| Shell Size | Max. Recommended Torque (Inch Pounds) Composite | A Dia. Max. | B Dia. Max. | C Dim. Max. |
|------------|---|--------------|--------------|-------------|
| 08 | 40 | .478 (12.1) | .358 (9.1) | .910 (23.1) |
| 10 | 40 | .599 (15.2) | .486 (12.3) | .910 (23.1) |
| 12 | 40 | .758 (19.3) | .603 (15.3) | .910 (23.1) |
| 14 | 40 | .882 (22.4) | .728 (18.5) | .910 (23.1) |
| 16 | 40 | 1.007 (25.6) | .853 (21.7) | .910 (23.1) |
| 18 | 40 | 1.133 (28.8) | .958 (24.3) | .910 (23.1) |
| 20 | 80 | 1.257 (31.9) | 1.083 (27.5) | .910 (23.1) |
| 22 | 80 | 1.382 (35.1) | 1.208 (30.7) | .910 (23.1) |
| 24 | 80 | 1.507 (38.3) | 1.333 (33.9) | .910 (23.1) |

NOTES

1. Also mates with 40M38277.
2. Metric dimensions (mm) are indicated in parentheses.
3. Material: Case hardened carbon steel with electroless nickel finish.
4. Receptacle and plug holder drives: 1/4" - Shell sizes 08, 10 and 12; 3/8" - Shell sizes 14 and up.