



**NOTES:**

1. For Thread (Table I) or Conduit (Table II) sizes not shown, please consult factory for availability.
2. Dimensions of "C" and "G2" Hex Flats may vary based on "A" Thread and Conduit size ordered. "C" Hex Flats will be determined by the larger of the two, but no smaller than "G2" specified in Table II.

Metric Dimensions (mm) are indicated in parentheses.

**712-462**  
**Glenair *FIRST* Swivel Stuffing Tube Fitting**  
**Mates with Series 75 Metal-Core Conduit (750-145 & 750-147)**



**TABLE I**

Size Letter Designator	A Thread Class 2B	B I.D.	C Hex Flats Min	D Dim	D Dim
A	7/8-12 UN	.406 (10.3)	1.130 (28.7)	.190 (4.8)	1.060 (26.9)
B	1-12 UNF	.515 (13.1)	1.130 (28.7)	.190 (4.8)	1.060 (26.9)
C	1 1/8-12 UNF	.640 (16.3)	1.250 (31.8)	.190 (4.8)	1.060 (26.9)
D	1 1/4-12 UNF	.750 (19.1)	1.380 (35.1)	.190 (4.8)	1.060 (26.9)
E	1 1/4-12 UNF	.812 (20.6)	1.380 (35.1)	.190 (4.8)	1.060 (26.9)
F	1 5/16-12 UN	.843 (21.4)	1.500 (38.1)	.190 (4.8)	1.190 (30.2)
G	1 1/2-12 UNF	.953 (24.2)	1.750 (44.5)	.190 (4.8)	1.190 (30.2)
J	1 5/8-12 UN	1.062 (27.0)	1.880 (47.8)	.190 (4.8)	1.190 (30.2)
K	1 3/4-12 UN	1.171 (29.7)	1.880 (47.8)	.190 (4.8)	1.500 (38.1)
L	1 13/16-12 UN	1.265 (32.1)	2.000 (50.8)	.190 (4.8)	1.500 (38.1)
M	2-12 UN	1.406 (35.7)	2.250 (57.2)	.250 (6.4)	1.500 (38.1)
N	2 1/16-12 UN	1.515 (38.5)	2.250 (57.2)	.250 (6.4)	1.560 (39.6)
P	2 3/16-12 UNS	1.625 (41.3)	2.380 (60.5)	.250 (6.4)	1.560 (39.6)
R	2 5/16-12 UNS	1.750 (44.5)	2.500 (63.5)	.250 (6.4)	1.560 (39.6)

**TABLE II**

Dash Number	E Ref	G1/G2 Hex Flats
16	.500 (12.7)	1.370 (34.8)
24	.750 (19.1)	1.620 (41.1)
32	1.000 (25.4)	2.000 (50.8)
40	1.125 (28.6)	2.250 (57.2)
48	1.500 (38.1)	2.750 (69.9)

**TABLE III: MATERIAL AND FINISH**

Symbol	Material	Finish
<b>ZN</b>	Aluminum Alloy	Zinc Nickel (500-Hour Salt Spray)
<b>BZN</b>	Brass	
<b>Z21</b>	316 Cres	Passivate

Metric Dimensions (mm) are indicated in parentheses.