



APPLICATION NOTES

- To be identified with manufacturer's name, part number and date code, space permitting.
- Front panel mount square flange receptacle with through mounting holes.
- Material/Finish:
Shell* - Fused tin over ferrous steel/Z1 passivated stainless steel.
Contacts - 52 Nickel alloy/gold plate
Seals - Silicone elastomer/N.A.
Insulation - Glass beads, NOIBN/N.A.
- Glenair 250-013 will mate with any MIL-DTL-5015 Series threaded coupling plug of same size and insert polarization.
- Performance:
Hermeticity - $<1 \times 10^{-7}$ cc/Sec @ 1 Atm. differential.
Dielectric Withstanding Voltage - See Table II.
Insulation Resistance - 5000 Megohms min @ 500VDC.
- Metric Dimensions (mm) are indicated in parentheses.

* Additional shell materials available, including titanium and Inconel®. Consult factory for ordering information.

250-013
MIL-DTL-5015 Type Hermetic
Threaded Coupling Box Mount Receptacle Connector
MS3142 Type



MIL-DTL
5015 Type

TABLE I: CONTACT DIMENSIONS					
Contact Size	X Max	Y Max	Z Min	V Min	W Max
16	.219 (5.6)	.375 (9.5)	.020 (0.5)	.065 (1.7)	.115 (2.9)
12	.281 (7.1)	.516 (13.1)	.020 (0.5)	.096 (2.4)	.190 (4.8)
8	-	.719 (18.3)	-	-	-
4	-	.980 (24.9)	-	-	-
0	-	.980 (24.9)	-	-	-

TABLE II: SERVICE RATING	
Service Rating	Working Voltage (Volts RMS)
INST	200
A	500
D	900
E	1250
B	1750
C	3000

HERMETIC LEAK RATE MOD CODES	
Designator	Required Leak Rate
-585A	1 x 10 ⁻¹⁰ cc's Helium per second
-585B	1 x 10 ⁻⁹ cc's Helium per second
-585C	1 x 10 ⁻⁸ cc's Helium per second

TABLE III: CONNECTOR DIMENSIONS							
Size	L Maximum Contact Size		ØN +.000 -.062 (+0 -1.6)	ØO (Ref) Mounting Hole	R T.P C — C	S ±.031 (0.8)	ØT ±.005 (0.1)
	16, 12, 8	4, 0					
8S	.730 (18.5)	-	.532 (13.5)	.562 (14.3)	.594 (15.1)	.875 (22.2)	.120 (3.0)
10S	.730 (18.5)	-	.656 (16.7)	.688 (17.5)	.719 (18.3)	1.000 (25.4)	.120 (3.0)
10SL	.730 (18.5)	-	.656 (16.7)	.688 (17.5)	.719 (18.3)	1.000 (25.4)	.120 (3.0)
12S	.730 (18.5)	-	.782 (19.9)	.812 (20.6)	.812 (20.6)	1.094 (27.8)	.120 (3.0)
12	.915 (23.2)	-	.782 (19.9)	.812 (20.6)	.812 (20.6)	1.094 (27.8)	.120 (3.0)
14S	.730 (18.5)	-	.906 (23.0)	.938 (23.8)	.906 (23.0)	1.188 (30.2)	.120 (3.0)
14	.915 (23.2)	-	.906 (23.0)	.938 (23.8)	.906 (23.0)	1.188 (30.2)	.120 (3.0)
16S	.730 (18.5)	1.040 (26.4)	1.032 (26.2)	1.062 (27.0)	.969 (24.6)	1.281 (32.5)	.120 (3.0)
16	.915 (23.2)	1.040 (26.4)	1.032 (26.2)	1.062 (27.0)	.969 (24.6)	1.281 (32.5)	.120 (3.0)
18	.915 (23.2)	1.040 (26.4)	1.156 (29.4)	1.188 (30.2)	1.062 (27.0)	1.375 (34.9)	.120 (3.0)
20	.915 (23.2)	1.040 (26.4)	1.282 (32.6)	1.312 (33.3)	1.156 (29.4)	1.500 (38.1)	.120 (3.0)
22	.915 (23.2)	1.040 (26.4)	1.406 (35.7)	1.483 (36.5)	1.250 (31.8)	1.625 (41.3)	.120 (3.0)
24	.915 (23.2)	1.040 (26.4)	1.532 (38.9)	1.562 (39.7)	1.375 (34.9)	1.750 (44.5)	.147 (3.7)
28	.915 (23.2)	1.040 (26.4)	1.782 (45.3)	1.812 (46.0)	1.562 (39.7)	2.000 (50.8)	.147 (3.7)
32	.915 (23.2)	1.040 (26.4)	2.032 (51.6)	2.062 (52.4)	1.750 (44.5)	2.250 (57.2)	.173 (4.4)
36	.915 (23.2)	1.040 (26.4)	2.282 (58.0)	2.312 (58.7)	1.938 (49.2)	2.500 (63.5)	.173 (4.4)
40	.915 (23.2)	1.040 (26.4)	2.532 (64.3)	2.562 (65.1)	2.188 (55.6)	2.750 (69.9)	.173 (4.4)
44	.915 (23.2)	1.040 (26.4)	2.782 (70.7)	2.812 (71.4)	2.375 (60.3)	3.000 (76.2)	.173 (4.4)
48	.915 (23.2)	1.040 (26.4)	3.032 (77.0)	3.062 (77.8)	2.625 (66.7)	3.250 (82.6)	.173 (4.4)

F