


New Contact Arrangements For Mod 38999 Style



**Marking for Plug Side, Removable Face (ASR), Shown
 Receptacle Side - Opposite**

NOTE: Each arrangement includes two guide pins and a threaded center jack post. The jack post is located at the center point of the X and Y axis. The alignment pins are located at the outer most points on the X axis.

TABLE I: MATERIAL AND FINISH		
SYM	MATERIAL	FINISH DESCRIPTION
M*	Aluminum	Electroless Nickel
MT		Nickel - PTFE
NF		Cadmium, Olive Drab
ZNU		Zinc-Nickel, Black
XM*	Composite	Electroless Nickel
XMT		Nickel - PTFE
XO		No Plating
XW		Cadmium, Olive Drab
XZN		Zinc-Nickel, Black
ZL*	Stainless Steel	Electro-Deposited Nickel
Z1*		Passivate

*RoHS Compliant

NOTES: Jam Nut for composite Jam Nut Mount Receptacle is Aluminum and plated same as connector shell.

"XO" Finish composite Jam Nut Receptacle is supplied with Unplated Composite Jam Nut and accommodates .093 maximum panel thickness.