

Standard Finishes		
GLENAIR SYMBOL	FINISH	SPECIFICATION(S)
B	Cadmium Plate, Olive Drab	AMS-QQ-P-416, Type II, Class 3
C*	Anodize, Black	MIL-A-8625, Type II, Class 2
G*	Hard Coat, Anodic	MIL-A-8625, Type III, Class 1
J	Iridite, Gold Over Cadmium Plate Over Electroless Nickel	MIL-C-5541, Class 3 AMS-QQ-P-416, Type II, Class 3 AMS-C-26074
LF	Cadmium Plate, Bright Over Electroless Nickel	1000 Hour Corrosion Resistance
M	Electroless Nickel	AMS-C-26074
N	Cadmium Plate, Olive Drab Over Electroless Nickel	AMS-QQ-P-416, Type II, Class 3 AMS-C-26074
NC	Zinc Cobalt, Dark Olive Drab	96 Hour Corrosion Resistance, Color Dark Olive Drab
NF	Cadmium Plate, Olive Drab Over Electroless Nickel	1000 Hour Corrosion Resistance
R*	Red Anodize	MIL-A-8625, Type II, Class 2
S*	Green Anodize	MIL-A-8625, Type II, Class 2
T	Cadmium Plate, Bright Over Electroless Nickel	AMS-QQ-P-416, Type II, Class 3 AMS-C-26074
U**	Cadmium Plate, Black	AMS-QQ-P-416, Type II, Class 3
UC	Zinc Cobalt, Black	96 Hour Corrosion Resistance, Color Black
V*	Blue Anodize	MIL-A-8625, Type II, Class 2
Y	Gold Iridite over Cadmium	MIL-C-5541, Class 3 over QQP-416, Type I, Class 3
Z1**	Passivate	AMS-QQ-P-35
ZN	Zinc Nickel, Olive Drab	Zinc Alloy per ASTM B 841-91, Class 1, Type E, Grade 3, Over Electroless Nickel, per AMS-C-26074

* Anodize finish; not suitable for EMI shielding or grounding applications.

** Applicable to corrosion resisting steel backshells and accessories. Consult factory for other available finishes.