



TABLE I

Dash No.	A Thread Iso Metric	B Dia	C Max	D Dia	E Ref	Max Entry Table II
01	M16 X 1.5 - 6g	.394 (10.0)	.827 (21.0)	.640 (16.3)	.593 (15.1)	03
02	M20 X 1.5 - 6g	.551 (14.0)	1.063 (27.0)	.802 (20.4)	.755 (19.2)	04
03	M27 X 2.0 - 6g	.949 (24.1)	1.496 (38.0)	1.077 (27.4)	1.027 (26.1)	07
04	M36 X 2.0 - 6g	1.181 (30.0)	1.850 (47.0)	1.438 (36.5)	1.388 (35.3)	08

TABLE II

Dash No.	F +.030 (.8) -.000 (.0)	G Max	Raychem Shrink Boot Part No.
01	.125 (3.2)	.531 (13.5)	202K121-100/180-0
02	.250 (6.4)	.656 (16.7)	202K121-100/180-0
03	.375 (9.5)	.781 (19.8)	202K132-100/180-0
04	.500 (12.7)	.906 (23.0)	202K142-100/180-0
05	.625 (15.9)	1.031 (26.2)	202K142-100/180-0
06	.750 (19.1)	1.156 (29.4)	202K163-100/180-0
07	.875 (22.2)	1.281 (32.5)	202K163-100/180-0
08	1.000 (25.4)	1.406 (35.7)	202K174-100/180-0

TABLE III

Finish Symbol	Finish Description
XM	Electroless Nickel
XW	Cadmium Olive Drab Over Electroless Nickel
XO	No Plating - Non-Conductive
XZN	Zinc Nickel - Olive Drab

- Metric dimensions (mm) are indicated in parentheses.
- Materials:

Adapter, Hex Nut, and Rear Nut -
Hi-Grade Engineering Thermoplastic.
Washer - Cres/Passivate.
O-Ring - Silicone