

PRODUCT SELECTION GUIDE

**MWDM Solder Cup Connectors**


Always in stock, these connectors feature gold-plated solder cup contacts for termination to #24 through #30 AWG wire.



*Solder Cup  
Page B-2*

**MWDM Pre-Wired Connectors**


These connectors avoid the expense and workmanship issues with soldering wires. Crimp terminations assure consistent circuit resistance. Stocked in #26 AWG, available in #24 gage to #30 gage wire.



*Pre-Wired  
Page B-4*

**MWDM Back-To-Back Unshielded Cables**


If a simple jumper cable is required, these cable assemblies simplify ordering. No special part numbers are necessary. Available in all sizes. Wiring is #1 to #1, etc. Back-to-backs are built to order in any length.



*Back-To-Back  
Page B-6*

**MWDM Shielded Cable Assemblies**


Featuring special Micro-D connectors with integral shield attachment platforms and ground springs, these shielded cable assemblies are terminated, tested and ready for immediate use.



*Shielded  
Cables  
Page B-8*

**MWDM Uninsulated Wire Pigtails**

Gold plated or solder dipped single strand uninsulated wire can be used for a variety of termination techniques, including wire bonding, flexible circuits and rigid boards.



*Uninsulated  
Wire  
Page B-12*

**GMDE Environmentally Sealed Panel Mount**

GMDE connectors are special Micro-D connectors with O-rings for sealing to panels or bulkheads.



*Environ-  
mental  
Page B-14*