


## Section J: Well-Master™ 260 High Temperature Micro-D GHTM



+260°C PCB Header

+260°C Cable Connector

- +260°C Operating Temperature
- Angled Mounting Ears to Fit in Small Diameter Instruments
- High Reliability TwistPin Contact System with Special High Temperature Alloy
- .050" Pitch Contact Spacing for Reduced Size
- Solder Cup, Pre-Wired or PCB


# Glenair Well-Master™ 260 Micro-D Withstands Extreme High Temperature

Standard Micro-D connectors are rated for +125°C. Glenair's MWDM Micro-D can withstand +150°C continuous operating temperature and can be upgraded to +200°C if assembled with special high temperature epoxies. But oil, gas and geothermal wells can subject electronic instruments to temperatures as high as +260°C. The GHTM Series Micro-D meets the need for a high density, high performance connector capable of handling this temperature. The GHTM features contacts made from a special alloy that resists softening when exposed to temperatures up to +260°C (500° F). Rugged passivated stainless steel shells and hardware, high temperature liquid crystal polymer (LCP) insulators and special epoxies allow these connectors to survive the most demanding environments. Unique angled mounting ears allow the Well-Master 260 to fit in confined spaces.


### GHTM HIGH TEMPERATURE CONTACT ARRANGEMENTS




9




15




21



25



31



37

**Mating face of pin connector. Socket connector contact numbers are reversed.**

#### MATERIALS AND FINISHES

Contacts	Proprietary nickel alloy, gold plated
Insulators	Liquid crystal polymer (LCP)
Shell	Stainless steel, passivated
Mounting Hardware	Stainless Steel
Potting Compound	Epoxy
Insulated Wire	Nickel-coated copper, PTFE insulation per M22759/87 (260°C)

#### SPECIFICATIONS

Current Rating	3 Amps
Contact Resistance	8 milliohms maximum
Dielectric Withstanding Voltage	600 Vac sea level
Insulation Resistance	5000 megohms minimum
Operating Temperature	-55° C. to +260° C.
Shock	50 g.
Vibration	20 g.