


Index of Filter Connector Products and Part Numbers



Section A: EMI/EMP Filter Connectors Introduction & Product Selection Guide

Product Selection Guide.....	A-1
Practical Solutions for Electromagnetic Compatibility.....	A-2
Application Checklist.....	A-3
EMC Materials and Technologies.....	A-4
EMI/EMP Filter Connector Overview.....	A-8
Multilayer Ceramic Planar Capacitor Arrays.....	A-10
EMI Filter and Transient Voltage Suppression Packaging.....	A-11
Transient Voltage Suppression Workshop with Serge Gigawatt.....	A-14
TVS Diode Selection Guide.....	A-16
Insertion Loss and Capacitance Values.....	A-18
Space-Grade Applications, Soldering and Lightning Strike.....	A-20
EMI/EMP Glossary.....	A-21
RoHS Compliance & Preference for Domestic Specialty Metals Statement.....	A-23
Diode Burn-In Services.....	A-24

Section B: Military Standard Type Circular Filter Connectors

Product Features.....	B-1
MIL-DTL-38999 Series I Type How To Order.....	B-2
MIL-DTL-38999 Series I Type Reference Information.....	B-3
240-381W MIL-DTL-38999 Series I Type Wall Mount.....	B-4
240-381R MIL-DTL-38999 Series I Type Crimp Removable Wall Mount.....	B-6
240-381J MIL-DTL-38999 Series I Type Jam Nut.....	B-8
240-381A MIL-DTL-38999 Series I Connector Adapter.....	B-10
MIL-DTL-38999 Series II Type Low-Profile Filter Connector How to Order.....	B-12
240-382 MIL-DTL-38999 Series II Reference Information.....	B-13
240-382W MIL-DTL-38999 Series II Wall Mount.....	B-14
240-382J (Hermetic Version Shown) MIL-DTL-38999 Series II Jam Nut.....	B-16
240-382A MIL-DTL-38999 Series II Connector Adapter.....	B-18
MIL-DTL-38999 Series III Type Filter Connector How to Order.....	B-20
MIL-DTL-38999 Series III Type Filter Connector Reference Information.....	B-21
240-383P MIL-DTL-38999 Series III Plug.....	B-22
240-383W MIL-DTL-38999 Series III Wall Mount.....	B-24
240-383J MIL-DTL-38999 Series III Jam Nut.....	B-26
240-383S MIL-DTL-38999 Series III Jam Nut Version with Crimp Contacts.....	B-28
240-383D MIL-DTL-38999 Series III Dual Flange Wall Mount with P.C. Tails.....	B-30
240-383E MIL-DTL-38999 Series III Dual Flange Jam Nut.....	B-32
240-383R MIL-DTL-38999 Series III Wall Mount with Crimp Contacts.....	B-34
240-383A MIL-DTL-38999 Series III Connector Adapter.....	B-36
MIL-DTL-38999 Series IV Type Filter Connector How to Order.....	B-38
MIL-DTL-38999 Series IV Type Filter Connector Reference Information.....	B-39
240-384J MIL-DTL-38999 Series IV Jam Nut Filter Connector.....	B-40
240-384W MIL-DTL-38999 Series IV Wall Mount.....	B-42
Glenair MIL-DTL-26482 Series II Type Filter Connector How to Order.....	B-44
Glenair MIL-DTL-26482 Series II Type Filter Connector Reference Information.....	B-45
240-264W MIL-DTL-26482 Series II Wall Mount.....	B-46
240-264J MIL-DTL-26482 Series II Jam Nut.....	B-48
240-264A Glenair MIL-DTL-26482 Series II Type Connector Adapter.....	B-50
Glenair MIL-DTL-83723 Series III Type Filter Connector How to Order.....	B-52
240-837W MIL-DTL-83723/83 Series III Wall Mount Filter Receptacle.....	B-54
240-837A MIL-DTL-83723 Series III Type Connector Adapter.....	B-56

Section C: Glenair Series 80 "Mighty Mouse" Filter Connectors

Product Features.....	C-1
Series 80 "Mighty Mouse" Key Positions and Panel Cut-Out Dimensions.....	C-2
Series 80 "Mighty Mouse" Contact Arrangements.....	C-3
Series 80 "Mighty Mouse" Pin Connectors Printed Circuit Board Layouts.....	C-4
Series 80 "Mighty Mouse" Socket Connectors Printed Circuit Board Layouts.....	C-5
Glenair Series 801 "Mighty Mouse" How to Order.....	C-6
240-801-01 and -07 Series 801 "Mighty Mouse" Banding Platform Versions.....	C-7
240-801-02 and -08 Series 801 "Mighty Mouse" Accessory Thread Versions.....	C-8

Glenair Series 804 "Mighty Mouse" How to Order.....	C-9
240-804-07 and -08 804 Style "Mighty Mouse" Receptacles.....	C-10
Glenair Series 805 "Mighty Mouse" How to Order.....	C-12
240-805-07 and -08 Series 805 "Mighty Mouse" Jam Nut Receptacles.....	C-13
240-805-01 and -02 Series 805 "Mighty Mouse" Square Flange Receptacles.....	C-14

Section D: Micro-D Subminiature Filter Connectors

Product Features.....	D-1
Micro-D Contact Arrangements, Materials and Performance Specifications.....	D-2
Micro-D Filter Connectors Filter Classes and Performance.....	D-3
Micro-D Filter Connectors Recommended Panel Cutouts.....	D-4
MIL-STD-681 Color Code Chart.....	D-5
240-030 Micro-D Filter Connectors Solder Cup.....	D-6
240-031 Micro-D Filter Connectors Vertical Mount Printed Circuit Board.....	D-8
240-031 Micro-D Filter Connectors Vertical Mount PCB Hardware Options.....	D-10
240-031 Micro-D Filter Vertical Mount PCB Pin Connector Layouts.....	D-11
240-032 Micro-D Filter Connectors Pre-Wired Pigtailed with Insulated Wire.....	D-12
240-033 Micro-D Filter Connectors Pin-Socket In-Line Filter Adapters.....	D-14
240-034 Micro-D Filter Connectors Right Angle Printed Circuit Board.....	D-16
240-034 Micro-D Filter Right Angle PCB Pin Connector Layouts.....	D-18
240-034 Micro-D Filter Right Angle PCB Socket Connector Layouts.....	D-19

Section E: MIL-C-24308 Type D-Subminiature Filter Connectors

Product Features.....	E-1
240-021 MIL-DTL-24308 Type D-Subminiature Connector.....	E-2
247-167 MIL-DTL-24308 Type Right Angle D-Subminiature Connector.....	E-4

Section F: 5015 Type Glenair ITS Series Power and Signal Connectors

Product Features.....	F-1
240-ITS-J 5015 Type ITS Series Jam Nut Mount, Reverse Bayonet Coupling.....	F-2
240-ITS-W 5015 Type ITS Series Wall Mount, Reverse Bayonet Coupling.....	F-4
240-515-J 5015 Type ITS Series Jam Nut Mount Receptacle Connector.....	F-6
240-515-W 5015, MS3452 ITS SeriesType Wall Mount Receptacle Connector.....	F-8

Section G: Special Purpose and Custom EMI/EMP Filter Connectors

Product Features.....	G-1
247-039 D38999 Series 1.5 Filtered Wall Mount Receptacle.....	G-2
247-026 D38999 Series III Hybrid Fiber Optic/Electrical Jam Nut Mount.....	G-4
247-045 Dual Bay Micro-D Filter Connector (90°) PCB Mount.....	G-6
247-070 Immersion Proof Micro-D Filter Connector (90°) PCB Mount.....	G-8
240-050 ARINC 600 Class A Size 3 Filter Receptacle.....	G-10

Section H: EMI/EMP Shielding Accessories

Product Features.....	H-1
Table I: Backshell Interface Dimensions.....	H-2
600-058 and 600-061 BAND-IT® Hand Banding Tools.....	H-3
BAND-IT® EMI Shield Termination Instructions.....	H-4
600-052, 600-057, 600-090, and 600-083 BAND-IT® Clamping Bands.....	H-5
319-064 Composite Swing-Arm Backshell with Nickel/Copper EMI Shield Sock.....	H-6
319-065 Composite Swing-Arm Backshell with Composite EMI Shield Sock.....	H-8
319-138 Composite "Wide Mouth" Swing-Arm Backshell w/ EMI Shield Sock.....	H-10
Composite Swing-Arm Assembly Instructions.....	H-12
380-107 EMI Non-Environmental Split Shell Backshell with Strain Relief.....	H-14
440-069 EMI/RFI Banding Adapter - Full Radius Profile.....	H-16
440-069 EMI/RFI Banding Adapter - Split Shell.....	H-18
440-075 EMI/RFI Banding Adapter - Standard Profile.....	H-20
687-207 Composite MIL-C-85049/93 Banding Split-Ring.....	H-22
103-026 and -027 Composite AmberStrand® Tubular Braid for EMI Shielding.....	H-23
100-001 Tubular Metal Braid Tin Coated Copper.....	H-24
100-003 Tubular Metal Braid Nickel Plated Copper.....	H-26
249-001 Conductive O-Ring for Jam Nut Receptacle Connectors.....	H-28
249-002 Conductive Gasket for Wall Mount Receptacle Connector.....	H-30