













257-003, 257-005, 257-007 and 257-012
Insert Arrangements & Misc. Information
(Face View of Pin Insert Shown)



Insert Arrangement	10SL-4	10SL-3	12-10	14S-2	14S-5
Contact Size & Quantity	2 - #16	3 - #16	10 - #20	4 - #16	5 - #16
MS Service Rating	A	A	INST	INST	INST
Alternative Position	N/A	N/A	N/A	X & Y	X



Insert Arrangement	14S-6	16S-1	18-1	20-29	24-11
Contact Size & Quantity	6 - #16	7 - #16	10 - #16	17 - #16	6 - #12, 3 - #8
MS Service Rating	INST	A	4A 6 INST	A	A
Alternative Position	N/A	W & Z	W, X, Y & Z	W & Z	W,X,Y & Z

TABLE III

Barrel and Rear Accy Hdwr.	Passivated Stainless Steel
Coupling Nut	Nickel/Aluminum/Bronze
Insulator, O-Ring, Grommet	Nitrile/Neoprene
Contacts	Gold Plated Copper Alloy With Solder Pots
Contact Current Rating	#20-5 Amps #16-10 Amps #12-17 Amps #8-35 Amps
Rated Operating Voltage	Service Rating INST - 250 VDC Service Rating A - 700 VDC
Dielectric Withstanding Voltage (Hi-Pot)	Service Rating INST - 1000 VRMS Service Rating A - 2000 VRMS
Insulation Resistance	5000 Megohms minimum at 500 VDC and +25°C
Temperature Range	-55°C to +125°C