




850-334-20-22
M39029/58-363 Type
Size 20 Pin Contact with Size 22 Crimp Barrel



Mating End Size	Glenair Part Number	Wire Size
20	850-334-20	-22



D

Material and Finish

Contact Body: Copper alloy / gold plated IAW ASTM B 488, Type II, code C, .000050
 Min thick, over nickel IAW SAE AMS-QQ-N-290, Class 2, .000030 to .000150 thick.

Crimp Tooling Data

Basic Crimptool: M22520/2-01
 Positioner: M22520/2-10

Notes

Contacts shall meet or exceed the applicable requirements specified in AS39029/58-363 except for 22AWG-28AWG crimp barrel.