


Series 22 Geo-Marine® Connectors Alternate Keyway Positions



INSERT ARRANGEMENTS

SHELL SIZE	SERIES 22 PATTERN	Dielectric Withstanding Voltage	CONTACT SIZE/QUANTITY				
			22	20	16	12	8
10	10-02	2300 Vdc			2		
10	10-04	1800 Vdc		4			
10	10-06	1800 Vdc		6			
10	10-13	1300 Vdc	13				
12	12-08	2300 Vdc			8		
12	12-10	1800 Vdc		10			
12	12-22	1300 Vdc	22				
14	14-04	2300 Vdc				4	
14	14-12	2300 Vdc			14		
14	14-19	1800 Vdc		19			
14	14-37	1300 Vdc	37				
16	16-06	2300 Vdc				6	
16	16-19	2300 Vdc			19		
16	16-26	1800 Vdc		26			
16	16-55	1300 Vdc	55				
18	18-08	1800 Vdc		8			
18	18-22	2300 Vdc			22		
18	18-32	1800 Vdc		32			
18	18-66	1300 Vdc	66				
20	20-11	2300 Vdc				11	
20	20-30	2300 Vdc			30		
20	20-41	1800 Vdc		41			
20	20-79	1300 Vdc	79				
22	22-19	2300 Vdc				19	
22	22-38	2300 Vdc			38		
22	22-55	1800 Vdc		55			
22	22-85	1300 Vdc	85				
24	24-48	2300 Vdc			48		
24	24-61	1800 Vdc		61			
24	24-100	1300 Vdc	100				
24	24-128	1300 Vdc	128				



FACE VIEW
RECEPTACLE

SHELL SIZE	ALTERNATE KEYWAY POSITIONS				
	DESIG.	N°	1°	2°	3°
10	90	76	62	118	104
12	90	70	58	122	110
14	90	69	56	124	111
16	90	72	60	120	108
18	90	72	62	120	108
20	90	72	60	120	108
22	90	75	64	116	105
24	90	75	64	115	105

DEPTH/PRESSURE CONVERSION CHART

FEET	METERS	P.S.I.	BAR
1	.3	.4	.0296
10	3.1	4.3	.2965
50	15.2	21.7	1.4962
100	30.5	43.3	2.9854
250	76.2	108.3	7.4670
500	152.4	216.5	14.9271
1,000	304.8	433.0	29.8543
1,500	457.2	649.5	44.7814
2,500	762.0	1082.5	74.6357
5,000	1524.0	2165.0	149.2715
10,000	3048.0	4330.0	298.5430
11,547	3519.5	5000.0	344.7379