

Series 800 Mighty Mouse with UN Mating Thread Overmolded Cordsets

800-034



Series 800



Abrasion-Resistant Polyurethane Jacket provides cold temperature flexibility and high strength. Low smoke/zero halogen material meets requirements for low toxicity.

90% Tinned Copper Braid is terminated directly to connector with stainless steel **BAND-IT®** strap.

Watertight Overmold provides strain relief and protection.

C

Series 800 Harsh Environment Shielded Cordsets

These overmolded cordsets withstand abrasion and chemical exposure. Low smoke zero halogen jacket reduces the amount of toxic and corrosive gasses emitted during combustion. Cable construction features silver coated stranded conductors with TFE insulation, tinned copper braid shield and extruded polyurethane jacket. Choose single-ended pigtails or double-ended "back-to-back" versions. Braid shield is attached directly to connector with **BAND-IT®** straps. Semi-rigid polyamide overmold provides strain relief and environmental sealing.

Series 801 cordsets are now available with size #20HD, #16 and #12 contacts. Ordering information is found on the following pages.

HARSH ENVIRONMENT CORDSET SPECIFICATIONS

Cable Jacket Material	Thermoplastic Polyurethane, Black, Low-Smoke, Zero-Halogen
Cable Shield	Tin-Coated Copper Braid, 90% Minimum Coverage
Conductors	Silver Coated Stranded Wire, TFE Insulated, Per M22759/11
BAND-IT® Shield Termination Band	Stainless Steel
Current Rating	#23 5 Amps, #20HD 7.5 Amps, #16 13 Amps, #12 23 Amps
Test Voltage (Dielectric Withstanding Voltage)	#23 500 VAC, #20HD 750 VAC, #16 and #12 1800 VAC Sea Level
Insulation Resistance	200 megohms minimum
Operating Temperature	-30° C. to +105° C.
Solvent Resistance, Polyamide Overmold	Excellent Resistance to Most Solvents, Fuels, and Oils; Poor Resistance to Strong Acids and Bipolar Solvents (Alcohol)
Shielding Effectiveness	50 dB minimum from 100MHz to 1000MHz.
Cable jacket Flammability and Toxicity	Toxicity Index 3.9 per NES 713 Oxygen Index 28% per ASTM D-2863 Smoke Index 24 per NES 711

Dimensions in inches (millimeters) and are subject to change without notice.

© 2010 Glenair, Inc.

CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912

www.glenair.com

C-21

E-Mail: sales@glenair.com

01-JANUARY-2010

Series 800 Mighty Mouse with UN Mating Thread Overmolded Cordsets

800-034 and 800-041

SERIES 800 CORDSETS WITH #23 CONTACTS

Sample Part Number									
800-034	-A	C	K	2	M	8-13	N	N	-36
Series	End A Connector	End B Connector	Plug Style	Wire Size	Shell Material / Finish	Insert Arr.	Protective Cover	Shell Key Pos.	Length
800-034 Overmolded Cordset, with Size #16 Contacts	-A Plug, with Male Pin Contacts	A Plug, with Male Pin Contacts	K Round Knurled Coupling Nut	2 #22 AWG	M Aluminum / Electroless Nickel	5-3 6-4	P Metal Protective Covers Included	N Normal	Overall Length In Inches 12 Inch Min.
	-B Plug, with Female Socket Contacts	B Plug, with Female Socket Contacts	KL Round Knurled Coupling Nut, Self-Locking	4 #24 AWG	NF Aluminum / Cadmium with OD Chromate	6-6 6-7	N No Covers Supplied	X Pos. X	
	-C Receptacle, with Male Pin Contacts	C Receptacle, with Male Pin Contacts	H Hex Coupling Nut		UCR Aluminum / Zinc- Cobalt with Black Chromate	7-10 8-13		Y Pos. Y	
	-D Receptacle, with Female Socket Contacts	D Receptacle, with Female Socket Contacts	HL Hex Coupling Nut, Self- Locking		ZNU Aluminum / Zinc- Nickel with Black Chromate	9-19 10-26 12-37		Z Pos. Z	
	-N Receptacle, with Female Socket Contacts	N No Connector (Single-Ended)	N Receptacle Cable		MT Aluminum / Nickel- PTFE				
					Z1 Stainless Steel / Passivated				

SERIES 800 CORDSETS WITH #20HD CONTACTS

Sample Part Number									
800-041	-A	C	K	0	M	8-28	N	N	-36
Series	End A Connector	End B Connector	Plug Style	Wire Size	Shell Material / Finish	Insert Arr.	Protective Cover	Shell Key Pos.	Length
800-041 Overmolded Cordset, with Size #16 Contacts	-A Plug, with Male Pin Contacts	A Plug, with Male Pin Contacts	K Round Knurled Coupling Nut	0 #20 AWG	M Aluminum / Electroless Nickel	6-23 7-25	P Metal Protective Covers Included	N Normal	Overall Length In Inches 12 Inch Min.
	-B Plug, with Female Socket Contacts	B Plug, with Female Socket Contacts	KL Round Knurled Coupling Nut, Self-Locking	2 #22 AWG	NF Aluminum / Cadmium with OD Chromate	8-28 9-210 12-220	N No Covers Supplied	X Pos. X	
	-C Receptacle, with Male Pin Contacts	C Receptacle, with Male Pin Contacts	H Hex Coupling Nut		UCR Aluminum / Zinc- Cobalt with Black Chromate			Y Pos. Y	
	-D Receptacle, with Female Socket Contacts	D Receptacle, with Female Socket Contacts	HL Hex Coupling Nut, Self- Locking		ZNU Aluminum / Zinc- Nickel with Black Chromate			Z Pos. Z	
	-N Receptacle, with Female Socket Contacts	N No Connector (Single-Ended)	N Receptacle Cable		MT Aluminum / Nickel- PTFE				
					Z1 Stainless Steel / Passivated				

Dimensions in inches (millimeters) and are subject to change without notice.

CAGE Code 06324

Printed in U.S.A.

**Series 800 Mighty Mouse with UN Mating Thread
Overmolded Cordsets
800-038 AND 800-039**



Series 800

SERIES 800 CORDSETS WITH #16 POWER CONTACTS

Sample Part Number									
800-038	-A	C	K	6	M	8-2	N	N	-36
Series	End A Connector	End B Connector	Plug Style	Wire Size	Shell Material / Finish	Insert Arr.	Protective Cover	Shell Key Pos.	Length
800-038 Overmolded Cordset, with Size #16 Contacts	-A Plug, with Male Pin Contacts	A Plug, with Male Pin Contacts	K Round Knurled Coupling Nut	6 #16 AWG	M Aluminum / Electroless Nickel	6-1 8-2	P Metal Protective Covers Included	N Normal	Overall Length In Inches 12 Inch Min.
	-B Plug, with Female Socket Contacts	B Plug, with Female Socket Contacts	KL Round Knurled Coupling Nut, Self-Locking	8 #18 AWG	NF Aluminum / Cadmium with OD Chromate	9-4 10-5 12-7	N No Covers Supplied	X Pos. X	
	-C Receptacle, with Male Pin Contacts	C Receptacle, with Male Pin Contacts	H Hex Coupling Nut		UCR Aluminum / Zinc-Cobalt with Black Chromate			Y Pos. Y	
	-D Receptacle, with Female Socket Contacts	D Receptacle, with Female Socket Contacts	HL Hex Coupling Nut, Self-Locking		ZNU Aluminum / Zinc-Nickel with Black Chromate			Z Pos. Z	
	N Receptacle, with Female Socket Contacts	N No Connector (Single-Ended)	N Receptacle Cable		MT Aluminum / Nickel-PTFE				
					Z1 Stainless Steel / Passivated				

SERIES 800 CORDSETS WITH #12 POWER CONTACTS


Sample Part Number									
800-039	-A	C	K	4	M	10-2	N	N	-36
Series	End A Connector	End B Connector	Plug Style	Wire Size	Shell Material / Finish	Insert Arr.	Protective Cover	Shell Key Pos.	Length
800-039 Overmolded Cordset, with Size #12 Contacts	-A Plug, with Male Pin Contacts	A Plug, with Male Pin Contacts	K Round Knurled Coupling Nut	2 #12 AWG	M Aluminum / Electroless Nickel	7-1 10-2	P Metal Protective Covers Included	N Normal	Overall Length In Inches 12 Inch Min.
	-B Plug, with Female Socket Contacts	B Plug, with Female Socket Contacts	KL Round Knurled Coupling Nut, Self-Locking	4 #14 AWG	NF Aluminum / Cadmium with OD Chromate	12-2 12-3	N No Covers Supplied	X Pos. X	
	-C Receptacle, with Male Pin Contacts	C Receptacle, with Male Pin Contacts	H Hex Coupling Nut		UCR Aluminum / Zinc-Cobalt with Black Chromate			Y Pos. Y	
	-D Receptacle, with Female Socket Contacts	D Receptacle, with Female Socket Contacts	HL Hex Coupling Nut, Self-Locking		ZNU Aluminum / Zinc-Nickel with Black Chromate			Z Pos. Z	
	N Receptacle, with Female Socket Contacts	N No Connector (Single-Ended)	N Receptacle Cable		MT Aluminum / Nickel-PTFE				
					Z1 Stainless Steel / Passivated				

Dimensions in inches (millimeters) and are subject to change without notice.




Series 800 Mighty Mouse with UN Mating Thread Overmolded Cordsets

Dimensions



RIGHT ANGLE CORDSETS



How To Order Right Angle Cordsets
 Insert the letter "R" after the End A or End B Connector letter designator.
Example
 Straight cable 800-034-ACH4Z16-4PN-72
 Right Angle 800-034-ARCRH4Z16-4PN-72

DIMENSIONS										
Shell Size	A Max.		B Max.		C Max.		D Max.		E Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
5	2.15	54.61	0.6	15.24	1.5	38.1	0.6	15.24	1.85	46.99
6	2.15	54.61	0.6	15.24	1.5	38.1	0.6	15.24	1.85	46.99
7	2.15	54.61	0.7	17.78	1.5	38.1	0.7	17.78	2.05	52.07
8	2.25	57.15	0.75	19.05	1.6	40.64	0.75	19.05	2.15	54.61
9	2.55	64.77	0.85	21.59	1.9	48.26	0.85	21.59	2.35	59.69
10	2.55	64.77	0.85	21.59	1.9	48.26	0.85	21.59	2.35	59.69
12	2.85	72.39	1.1	27.94	2.2	55.88	1.1	27.94	2.85	72.39

Dimensions in inches (millimeters) and are subject to change without notice.

CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912

www.glenair.com

C-24

E-Mail: sales@glenair.com