

Series 811 Mighty Mouse High Density (HD)
Metal Protective Covers
667-347 and 667-218



Protect Connectors From Damage

Machined aluminum covers have rubber gaskets for a watertight fit.

Stainless Steel Fittings and Rings Choose small diameter eye fittings for panel attachment. Larger rings fit under the jam nut or over cable jackets. Split rings can be installed on fully assembled cables.






Polyurethane-Coated SST Wire Rope

offers high strength, excellent abrasion resistance and good flexibility. Or, choose Teflon® jacket for high temperature exposure.

Braided Nylon Rope provides excellent flexibility and good abrasion resistance, and can be ordered with slip knot fittings for easy installation on any size cable.

HOW TO ORDER

Sample Part Number

| 667-347 | -M | -G | 9 | 04 | -6 |
|---|--|--|--|--|---|
| Series | Shell Material / Finish | Attachment Type | Shell Size | Attachment Code | Attachment Length in Inches |
|  667-347 Protective Cover for use with Series 811 Plugs | ME Aluminum / Electroless Nickel RoHS Compliant MT Aluminum / Nickel-PTFE RoHS Compliant ZR Aluminum / Zinc-Nickel with Black Chromate | -G Nylon Rope -H SST Wire Rope, Teflon® Jacket -N No Attachment -S SST Sash Chain -SK Nylon Rope With Slip Knot -T SST Wire Rope, No Jacket -U SST Wire Rope, Polyurethane Jacket "SST" = Stainless Steel | 5 6 7 8 9 | Omit for attachment Types N (No Attachment) and SK (Slip Knot) | Omit for attachment Type N (No Attachment) Example "6" equals six inch length |
| | | | |  Small Ring | |
|  667-218 Protective Cover for use with Series 811 Receptacles | | | |  Large Ring | 14 - .385 (9.78) I.D. 15 - .445 (11.30) I.D. 16 - .570 (14.48) I.D. 17 - .635 (16.13) I.D. 18 - .695 (17.65) I.D. 19 - .885 (22.48) I.D. 20 - 1.070 (27.17) I.D. 21 - 1.135 (28.83) I.D. 22 - 1.210 (30.73) I.D. 23 - 1.275 (32.39) I.D. 24 - 1.375 (34.94) I.D. |
| | | | | |  Split Ring |

Dimensions in Inches (millimeters) are subject to change without notice.