

Series 34 Shorting Cap Backshells

for Series 80 Mighty Mouse Connectors

340MS001 Shorting Cap Backshell, Spin Coupling



Spin coupling. Shorting cap backshell fits Series 80 Mighty Mouse connectors. Tether backshell with optional attachment strap and lanyard. Aluminum or stainless steel. Attachment strap and hardware are passivated stainless steel. Silicone O-ring.

Adapter Code M


This accessory fits Series 80 Mighty Mouse Connectors

ATTACHMENT TYPES

F		Wire Rope, Blue Nylon Jacket 6/6 nylon over stainless steel rope, stainless steel ring terminal, fair flexibility, good abrasion resistance, -55 to +100 °C
G		Nylon Rope Solid braided nylon cord, black, stainless steel ring terminal, very flexible, good abrasion resistance, good resistance to fuels, .120" (3mm) diameter, -55 to +100 °C
H		Wire Rope, Clear FEP Jacket Clear FEP jacket over SST rope, stainless steel ring terminal, fair flexibility, good abrasion resistance, .100" diameter, -55 to +200 °C
S		Sash Chain #8 sash chain, stainless steel
U		Wire Rope, Black Polyurethane Stainless steel rope with black polyurethane coating, stainless steel ring terminal, very flexible, excellent abrasion resistance, excellent resistance to fuels, .080" (2mm) diameter, -55 to +125 °C

PART NUMBER

Base P/N	340MS001	M	16	-2	F	10	A
Material/Finish	M Alum/ Electroless Nickel MT Alum/ Nickel-PTFE NF Alum/ Olive Drab Cadmium ZR Alum/ Black Zinc-Nickel TZ Alum/ Tin-Zinc ZI SST/ Passivated						
Shell Size	05 06 07 08 09 10 11 12 13 14 15 16 17 See table below						
Length	-2 1.0 inch -3 1.5 inches -4 2.0 inches -5 2.5 inches -6 3.0 inches -8 4.0 inches Length in 1/2 inch increments.						
Attachment Type	N No Attachment C Attachment Strap Only, No Lanyard F Wire Rope, Blue Nylon Jacket G Nylon Rope H Wire Rope, Clear FEP Jacket S Sash Chain U Wire Rope, Black Polyurethane Jacket						
Attachment Length	Omit for Attachment Types C and N Attachment Length in 1/2 inch increments. e.g., "11" = 5.5 inches.						
Lanyard Ring I.D.	Omit for Attachment Types C and N E .125 (3.2) ± .010 (0.3) A .140 (3.6) ± .010 (0.3) B .167 (4.2) ± .010 (0.3) C .182 (4.6) ± .010 (0.3) D .191 (4.9) ± .010 (0.3) F .218 (5.5) ± .010 (0.3)						



Shell Size Code	Shell Size		A	
	Series 800, 801, 803, 804	Series 805	Thread UNEF-2B	øB Max. in mm
05	5	N/A	0.250-32	.470 11.9
06	6	N/A	0.3125-32	.530 13.5
11	N/A	8	0.3750-32	.570 14.5
07	7	9	0.4375-28	.637 16.2
08	8	10	0.500-28	.700 17.8
09	9	11	0.5625-24	.758 19.3
10	10	12	0.625-24	.819 20.8
12	11, 12, 13	13	0.6875-24	.896 22.8
13	N/A	15	0.750-20	.930 23.6
14	14, 15, 16, 17	18, 19	0.9375-20	1.137 28.9
16	19	21	1.0625-18	1.230 31.2
17	21	23	1.1875-18	1.387 35.2

