

# 600-161 Digital Torque Wrench and 600-162 Bench Stand




Audible beeping warning sound when the forcing torque reaches 90%, 100%, and 110% of the set torque

Sliding clear protective cover helps to prevent accidental touching of function keys

Four Units: Ft-Lb, Nm, Kg-cm, In-Lb

99 Memories for easy tracking of the forced torques

Flashing warning lights enhance the audible warning beeps (See above)



## Hand-Held Digital Torque Wrench

3/8" Dual Drives Top and Bottom to facilitate bench mount operation  
Requires two AAA batteries

### 600-161

99 Presets available for torque level 29 to 310 inch pound range

Clockwise and counter-clockwise provide  $\pm 2\%$  accuracy

Torque range:

Ft-Lb = 2.5 ~ 25 Ft-Lb

N m = 3.3 ~ 35N.M

Kg-cm = 34 ~ 340 Kg-cm

In-Lb = 29 ~ 310 In-Lb

## Bench Stand

### 600-162

For Digital Torque Wrench 600-161

Vertical and Horizontal Mounting Options

Multi-Position Angle Adjustment



Shown with 600-161 Digital Torque Wrench in Position