

Series 66 Protective Covers

for Series 804 Mighty Mouse Connectors

809-198 Plug Cover

MM804 Plug Cover











809-198 protective cover fits Glenair Series 804 push/pull plug connectors. Aluminum or stainless steel, with stainless steel fittings. Gold plated stainless steel spring, fluorosilicone O-ring.

TABLE 1 MATERIAL / FINISH

Aluminum	Stainless Steel
C Black Anodize	Z1 Passivate
M Electroless Nickel	
NF Olive Drab Cadmium	
MT Nickel-PTFE	
ZR Black Zinc-Nickel	
TZ Tin-Zinc	

TABLE 2 ATTACHMENT TYPE

D	 SST Bead Chain .125 (3.2) diameter, size 6, -65 to +200 °C
F	 Wire Rope, Blue Nylon Jacket 6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C
G	 Black Nylon Rope Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter, -55 to +100 °C
H	 Wire Rope, Clear FEP Jacket Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C
S	 Sash Chain #8 sash chain, stainless steel. Length tolerance is ± one link .280 (Z1)
SK	 Nylon Rope with Slip Knot Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter. Length includes .5" (13mm) dia. loop, -55 to +100 °C
T	 SST Wire Rope, No Jacket Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C
U	 Wire Rope, Black Polyurethane Stainless steel rope with black polyurethane coating, flexible, excellent abrasion resistance and resistance to fuels, .080" (2mm) diameter, -55 to +125 °C

PART NUMBER

Base P/N	809-198	ZR	12	U	6	-04	R
Material/Finish	See Table 1						
Shell Size	5 6 7 8 9 10 12 14 15						
Attachment Type	-N No Attachment See Table 2 for Attachment Types						
Attachment Length	Omit for Attachment Type N Length in One Inch Increments						
Attachment Ring	Omit for Attachment Types N and SK See Table 3 for Attachment Ring Codes						
Keyway Position	Omit for Single Master Keyway A B C D E F						








TABLE 3 ATTACHMENT RING

EYELET		SOLID RING		SPLIT RING	CABLE TIE
					
Code	Eyelet I.D. ± .010 (0.3)	Code	Ring I.D. ± .015 (0.4)	Code	Ring I.D. ± .015 (0.4)
01	.125 (3.2)	32	.265 (6.7)	19	.885 (22.5)
02	.145 (3.7)	29	.315 (8.0)	26	.950 (24.1)
04	.182 (4.6)	14	.385 (9.8)	28	1.015 (25.8)
06	.197 (5.0)	15	.445 (11.3)	20	1.070 (27.2)
		33	.510 (13.0)	21	1.135 (28.8)
		16	.570 (14.5)	22	1.210 (30.7)
		17	.635 (16.1)	23	1.275 (32.4)
		18	.695 (17.7)	24	1.380 (35.1)
		27	.766 (19.5)	30	1.380 (35.1)
		31	.820 (20.8)	25	1.530 (38.9)
				50	.432 (11.0)
				52	.492 (12.5)
				54	.648 (16.5)
				56	.757 (19.2)
				58	.898 (22.8)
				60	1.023 (26.0)
				64	1.137 (28.9)
				68	1.357 (34.5)
					Code WS
					Black 6/6 nylon cable tie 1.77 (45.0) max. wire bundle dia.