


Swing-Arm® Clamps

for MIL-DTL-38999 Series I and II Connectors

870F003 Swing-Arm Saddle Clamp, Braid Sock, SST/Aluminum

CLAMP DIMENSIONS



Standard Clamp							Large Clamp						
Shell Size	K Max in	K Max mm	L Min in	L Min mm	M Ref. in	M Ref. mm	Shell Size	N Max in	N Max mm	P Min in	P Min mm	R Ref. in	R Ref. mm
08	.98	24.9	.22	5.6	.265	6.7	08	.98	24.9	.33	8.4	.356	9.0
10	1.05	26.7	.27	6.9	.310	7.9	10	1.20	30.5	.45	11.4	.422	10.7
12	1.20	30.5	.35	8.9	.422	10.7	12	1.45	36.8	.62	15.7	.637	16.2
14	1.30	33.0	.47	11.9	.538	13.7	14	1.54	39.1	.68	17.3	.707	18.0
16	1.44	36.6	.55	14.0	.590	15.0	16	1.60	40.6	.80	20.3	.759	19.3
18	1.56	39.6	.62	15.7	.660	16.8	18	1.73	43.9	.90	22.9	.841	21.4
20	1.69	42.9	.70	17.8	.744	18.9	20	1.95	49.5	1.05	26.7	.996	25.3
22	1.77	45.0	.78	19.8	.826	21.0	22	2.08	52.8	1.18	30.0	1.060	26.9
24	1.89	48.0	.85	21.6	.896	22.8	24	2.32	58.9	1.30	33.0	1.124	28.5

MATERIAL/FINISH

Aluminum (Codes M, MT, NF, TZ, ZR)

Coupling nut, body, arms, saddles, interface ring: aluminum

Crimp Ring: copper alloy/ tin plated

Screws, washers, inserts: stainless steel/ passivated

Anti-decoupling spring: thermoplastic

Clinch nuts: Codes M, MT, TZ and ZR: stainless steel, silver plated. Code NF: stainless steel/ olive drab cadmium

Stainless Steel (Codes BM, BMT, Z1, ZM)

Coupling nut, body, arms, saddles, anti-decoupling springs, screws, washers, inserts: stainless steel, passivated

Crimp Ring: copper alloy/ tin plated

Clinch nuts: stainless steel, silver plated

interface ring: brass (codes BM, BMT) or stainless steel (Z1, ZM)

Braid:


Code N: 34 AWG nickel-coated copper

Code T: 34 AWG tin-coated copper,

Code A: *AmberStrand*® ultralightweight nickel-coated polymer

Code L: *ArmorLite*® lightweight microfilament nickel-coated 316L stainless steel


INTERFACE RING AND BRAID



Shell Size	ø B Min in	ø B Min mm	Braid I.D. in	Braid I.D. mm
08	.264	6.7	.375	9.5
10	.392	10.0	.375	9.5
12	.506	12.9	.500	12.7
14	.631	16.0	.500	12.7
16	.756	19.2	.781	19.8
18	.844	21.4	.781	19.8
20	.970	24.6	1.000	25.4
22	1.094	27.8	1.000	25.4
24	1.219	31.0	1.250	31.8

SPLICE RING AND PRE-COILED BAND (K AND J OPTIONS)

Optional splice ring provides a reliable, low resistance method of splicing Swing-Arm braid sock to wire bundle braid. Snap splice ring over wire bundle, then overlap braid sock, pigtailed and cable braid. Install band around splice ring and braid using Band-Master ATS banding tool. *Slim Standard Band* is 50% lighter weight than standard band with no reduction in strength.



Shell Size	Band Part Number		Split Ring Part Number	øA		øB	
	Standard	Slim Standard		± .03 (0.8) in	± .03 (0.8) mm	± .03 (0.8) in	± .03 (0.8) mm
08	601-006	601-571	687-207XB04	.25	6.4	.40	10.2
10	601-006	601-571	687-207XB06	.38	9.7	.53	13.5
12	601-006	601-571	687-207XB08	.50	12.7	.65	16.5
14	601-006	601-571	687-207XB10	.63	16.0	.78	19.8
16	601-006	601-571	687-207XB12	.75	19.1	.90	22.9
18	601-041	601-572	687-207XB14	.88	22.4	1.03	26.2
20	601-041	601-573	687-207XB16	1.00	25.4	1.15	29.2
22	601-041	601-573	687-207XB18	1.13	28.7	1.28	32.5
24	601-041	601-573	687-207XB20	1.25	31.8	1.40	35.6

FIGURE 1
NF SELECTIVE FINISH

