

# MICRO-CRIMP RECTANGULAR CONNECTORS

## Series 790 High-Density



### Series 790 Material and Finish Options

The Series 790 Micro-Crimp® connector is available in five preferred finishes: electroless nickel, nickel-PTFE, tin-zinc, cadmium, and zinc-nickel.

Additional material and finish options are available. Replace the preferred plating code with the alternate code from the table below.

SERIES 790 SHELL FINISH OPTIONS					
	Electroless Nickel	Nickel-PTFE	Tin-Zinc	Olive Drab Cadmium	Black Zinc-Nickel
Glenair Code	<b>M</b>	<b>MT</b>	<b>TZ</b>	<b>N</b>	<b>ZR</b>
Corrosion Resistance	Fair	Excellent	Excellent	Excellent	Excellent
Salt Spray Hours	48	500	500	500	500
Conductivity	Excellent	Excellent	Very Good	Very Good	Very Good
RoHS Compliant <sup>(1)</sup>	Yes	Yes	Yes	No	Yes

<sup>(1)</sup> Does not contain cadmium or hexavalent chromium. Meets EU requirements.

#### TIN-ZINC PLATING

The United States Department of Defense (DOD) has mandated the elimination of cadmium from DOD weapons systems because of toxicity concerns. The European Union has also restricted the use of cadmium on electronics equipment (RoHS). Tin-Zinc is a RoHS cadmium-free sacrificial finish that offers high conductivity and shielding performance, corrosion resistance, solderability, and proven compatibility with legacy cadmium and zinc-nickel finishes. Tin-Zinc is DLA-qualified and RoHS compliant.

#### ALTERNATE SHELL MATERIAL AND FINISH CODES

Code	Shell Material	Shell Finish	Finish Specification	Salt Spray Hrs.	Electrical Conductivity	RoHS <sup>(1)</sup>
<b>C</b>	Alum	Anodize, Black	MIL-PRF-8625	48	Non-Conductive	✓
<b>E<sup>(2)</sup></b>	Alum	Chem Film, Gold	MIL-DTL-5541	168	Conductive	
<b>J</b>	Alum	Cadmium, Yellow	AMS-QQ-P-416	500	Conductive	
<b>Z1</b>	SST	Passivate	AMS2700	500	Conductive	✓
<b>Z2</b>	Alum	Gold	MIL-DTL-45204	48	Conductive	✓
<b>ZM</b>	SST	Electroless Nickel	AMS-C26074	500	Conductive	✓
<b>ZMT</b>	SST	Nickel-PTFE	AMS2454	1000	Conductive	✓
<b>ZW</b>	SST	Cadmium, Olive Drab	AMS-QQ-P-416	500	Conductive	
<b>ZZR</b>	SST	Zinc-Nickel, Black	ASTM B841	500	Conductive	✓

<sup>(1)</sup> Does not contain cadmium or hexavalent chromium. Meets EU requirements.

<sup>(2)</sup> Maximum temperature = +125°C