

MICRO-CRIMP RECTANGULAR CONNECTORS


Series 791 Scoop-Proof



240-791-005

Panel Receptacle, Filtered

- ◆ Solder cup termination
- ◆ Pin contacts



240-791-005 rear panel mount receptacle has ceramic filter array to attenuate unwanted signals. Solder cup contacts. Available with two filter types (C, Pi) and 11 filter classes ranging from 35 pF to 240K pF. O-ring provides ingress protection. Machined aluminum shell has rear threads for attaching EMI banding adapter (799-016, sold separately).

- Aerospace-grade filter connector with scoop-proof duo-lobe shell
- Ceramic planar array filter element
- 39 insert arrangements with M39029-type contacts
- Environmental

INSERT ARRANGEMENTS			
Insert Arrangement	No. of Contacts		
	#23	#16	#12
A-5	5		
B-2P2		2	
B-9	9		
C-13	13		
D-15	15		
D-3P3		3	
D-7P2	5	2	
E-11P2	9	2	
E-19	19		
E-7P3	4	3	
F-14P3	11	3	
F-15P2	13	2	
F-23	23		
F-5P5		5	
G-13P2	11		2
G-21P1	20		1
G-3P3			3
G-33	33		
H-10P4	6		4
H-29P7	22	7	
H-36P2	34		2
H-51P1	50		1
H-54P2	52	2	
H-5P5			5
H-66	66		
J-17P4	13	4	
J-25P2	23	2	
J-33	33		
J-7P7		7	
K-27P4	23	4	
K-35P2	33	2	
K-43	43		
K-9P9		9	
L-22P4	18		4
L-48P2	46		2
L-6P6			6
L-78	78		
M-17P17		17	
M-102	102		

HOW TO ORDER								
Sample Part Number		240-791-005P	H-66	ME	P	C	P	B
Basic Part Number	240-791-005P	Panel Receptacle, Filtered, Pin Contacts						
Shell Size-Insert Arr.	See “Insert Arrangements” Table							
Shell Finish	ME Electroless Nickel							
	MT Nickel / PTFE							
	NF Olive Drab Cadmium							
	TZ Tin-Zinc							
	ZR Black Zinc-Nickel							
Filter Type	C C Circuit							
	P Pi Circuit							
Filter Capacitance Class	See “Filter Capacitance Class ” Table							
Hardware Option	N No Hardware <i>Threaded holes</i>							
	P Female Jackposts							
Polarization Key Option	Enter Letter Designator for Position A, B, C, D, E , or F per Mod Code 555 (see page B-8 for details) Omit for none							

FILTER CLASS		
Filter Class	Capacitance Range (pF)	
	Filter Type P	Filter Type C
X*†	160,000-240,000	80,000-120,000
Y*	80,000-120,000	40,000-60,000
Z*	60,000-90,000	30,000-45,000
A	38,000-56,000	19,000-28,000
B	32,000-45,000	16,000-22,500
C	18,000-33,000	9,000-16,500
D	8,000-12,000	4,000-6,000
E	3,300-5,000	1,650-2,500
F	800-1,300	400-650
G	400-600	200-300
J	70-120	35-60

* Filter classes X, Y and Z are 250 VDC. All others are 500 VDC.
 † Class X filters not available for arrangements with 3 or more rows of contacts.

RATINGS	
■ Voltage (DWV): 500 VDC. Class X, Y, Z: 250 VDC.	
■ Current rating for arrangements with all contacts the same size: #23 5A, #16 13A, #12 23A	
■ Current rating for arrangements with mixed contact sizes: #23 5A, #16 7.5A, #12 13A	
■ Operating temperature: -55 to +125 °C	
■ Durability: 500 mating cycles	
■ Shock: 300 g	
■ Vibration: 20 g random	
■ Insulation resistance: 5000 megohm @ 200 VDC. Class X, Y, Z: 1000 megohm @ 83 VDC	

CONSTRUCTION	
■ Contacts: Copper alloy, gold over nickel finish	
■ Shell: Aluminum	
■ Insulators: High performance dielectric	
■ Interfacial seal: Fluorosilicone/silicone blend	
■ EMI spring: Stainless steel, gold plated	
■ O-ring: Fluorosilicone	
■ Hardware: Stainless steel	

MICRO-CRIMP RECTANGULAR CONNECTORS


Series 791 Scoop-Proof

SERIES™
791
Scoop-Proof

240-791-005

Panel Receptacle, Filtered

- ◆ Solder cup termination
- ◆ Pin contacts



Shell Size	A Max		B ± .005 (0.1)		C ± .005 (0.1)		D Max		E Max		F ± .005 (0.1)	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
A	1.565	39.8	1.150	29.2	.750	19.1	.490	12.4	.760	19.3	.565	14.4
B	1.715	43.6	1.300	33.0	.900	22.9	.640	16.3	.910	23.1	.715	18.2
C	1.865	47.4	1.450	36.8	1.050	26.7	.790	20.1	1.060	26.9	.865	22.0
D	1.940	49.3	1.525	38.7	1.125	28.6	.865	22.0	1.160	29.5	.965	24.5
E	2.090	53.1	1.675	42.5	1.275	32.4	1.015	25.8	1.310	33.3	1.115	28.3
F	2.240	56.9	1.825	46.4	1.425	36.2	1.165	29.6	1.460	37.1	1.265	32.1
G	2.200	55.9	1.785	45.3	1.388	35.3	1.127	28.6	1.410	35.8	1.215	30.9
H	2.835	72.0	2.375	60.3	1.900	48.3	1.516	38.5	2.045	51.9	1.800	45.7
J	2.615	66.4	2.200	55.9	1.800	45.7	1.540	39.1	1.810	46.0	1.615	41.0
K	2.990	75.9	2.575	65.4	2.175	55.2	1.915	48.6	2.210	56.1	2.015	51.2
L	3.075	78.1	2.611	66.3	2.136	54.3	1.752	44.5	2.281	57.9	2.036	51.7
M	3.345	85.0	2.824	71.7	2.200	55.9	1.815	46.1	2.445	62.1	2.200	55.9

Application Note
Polarization Key Positions
See Mod Code 555 pg. B-8 for details

Plug

Receptacle

HARDWARE DETAILS

N No Hardware

Tapped holes.
Size A-G, J, K = 6-32 UNC-2B
H, L = 8-32 UNC-2B
M = 10-32 UNF-2B
150 (3.8) min. depth

P Female Jackposts

Jackposts are non-removable.
Size A-G, J, K = 4-40 UNC-2B
H, L = 6-32 UNC-2B
M = 8-32 UNC-2B

Application Note
Panel Cutout
See page B-53 for panel cutout dimensions.

Application Note
EMI Banding Backshell 799-016
See page F-32 for backshell ordering information.