

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed

SERIES™
792
High-Speed

792-011

Panel Plug, 90° PC Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Socket contacts



792-011 panel plug has El Ochito® high-speed octaxial PC tail socket contacts for 90° thru-hole printed circuit board termination. Contacts are potted with epoxy. Machined aluminum shell has integral standoff and threaded holes for attachment to PC board. Combo arrangements have #23 contacts.

- Aerospace-grade rectangular PCB connector with high speed size 8 octaxial contacts
- 1–5 data ports
- Rugged duo-lobe aluminum shell
- Environmental

INSERT ARRANGEMENTS

Thermoplastic Insert	Grounded All-Aluminum	No. of Contacts	
		Ochito	#23
A-1P1	A-1G1	1	–
A-3P1		1	2
B-23P1		1	22
B-2P2	B-2G2	2	–
B-6P2		2	4
C-24P2		2	22
C-3P3	C-3G3	3	–
C-9P3		3	6
D-27P3		3	24
D-4P4	D-4G4	4	–
D-12P4		4	8
E-5P5	E-5G5	5	–
E-15P5		5	10
E-45P3		3	42

HOW TO ORDER

Sample Part Number		792-011S	E-45P3	M	G	AK	C	B
Basic Part Number	792-011S	Panel Plug, 90° PC Tails, Octaxial Socket Contacts						
Shell Size-Insert Arr.	See <i>“Insert Arrangements”</i> Table							
Shell Finish	M	Electroless Nickel						
	MT	Nickel / PTFE						
	NF	Olive Drab Cadmium						
	TZ	Tin-Zinc						
	ZR	Black Zinc-Nickel						
Hardware Option <i>Table 1</i>	N	No Hardware <i>Threaded holes</i>						
	G	Guide Pins <i>For blind mating</i>						
	P	Female Jackposts						
Protocol Code	See <i>“Protocol Code”</i> table on next page							
Panel O-Ring	N	No O-ring						
	C	Conductive Fluorosilicone O-ring						
	F	Fluorosilicone O-ring						
Polarization Key Option	Enter Letter Designator for Position A, B, C, D, E, F, G, H, J, or K per Mod Code 1104 (see page C-8 for details) Omit for none							

TABLE 1 HARDWARE OPTION

 N No Hardware Threaded Hole 10-32 UNF-2B, 150 (3.81) min. depth	 P Female Jackpost 8-32 UNC-2B	 G Guide Pin
--	---	------------------------

RATINGS

- Voltage (DWV): 100 VAC
- Current: #23 1A
- Operating temperature: -65 to +150 °C
- Durability: 500 mating cycles
- Shock: 300 g
- Vibration: 20 g random

CONSTRUCTION

- #23 Contacts: Copper alloy, gold over nickel finish, stainless steel hood
- Ochito contact: Copper alloy, gold over nickel finish. Insulators are high performance thermoplastic.
- Shell: Aluminum
- Insulator: High performance thermoplastic
- Encapsulant: Epoxy
- Hardware: Stainless steel, passivated
- O-ring: Fluorosilicone. Conductive O-ring is Cho-Seal 1298 silver-plated aluminum filled fluorosilicone.

Application Note

Polarization Key Positions

See Mod Code 1104 pg. C-8 for details



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed



792-011

Panel Plug, 90° PC Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Socket contacts

OCHITO PROTOCOLS



WHITE
1000BASE-T
10GBASE-T



BLUE
USB 3.0




RED
HDMI, SATA,
DisplayPort

The Ochito octaxial contact is color-coded to signify the data protocol. White is used for high speed Ethernet, blue is used for USB 3.0, and red is used for multi gigabit 100 ohm protocols including HDMI, DisplayPort and SATA. The connector part number includes a code from the **Protocol Code** table. This code enables combinations of protocols as shown in the examples below.




Code AE



Code AQ


PROTOCOL CODE

Code	Cavity				
	A1	A2	A3	A4	A5
AA	W	W	W	W	W
AB	B	W	W	W	W
AC	R	W	W	W	W
AD	B	B	W	W	W
AE	R	B	W	W	W
AF	R	R	W	W	W
AG	B	B	B	W	W
AH	R	B	B	W	W
AJ	R	R	B	W	W
AK	R	R	R	W	W
AL	B	B	B	B	W
AM	R	B	B	B	W
AN	R	R	B	B	W
AP	R	R	R	B	W
AQ	R	R	R	R	W
AR	B	B	B	B	B
AS	R	B	B	B	B
AT	R	R	B	B	B
AV	R	R	R	B	B
AW	R	R	R	R	B
AX	R	R	R	R	R



Shell Size	A Max		B ± .005 (0.1)		C Max		D ± .005 (0.1)		E ± .002 (0.05)		F Max	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
A	2.220	56.39	1.075	27.31	.615	15.62	1.699	43.15	.725	18.42	1.455	36.96
B	2.595	65.91	1.450	36.83	.990	25.15	2.074	52.68	1.100	27.94	1.830	46.82
C	2.970	75.44	1.825	46.36	1.365	34.67	2.449	62.20	1.475	37.47	2.205	56.01
D	3.345	84.96	2.200	55.88	1.740	44.20	2.824	71.73	1.850	46.99	2.580	65.53
E	3.720	94.49	2.575	65.41	2.115	53.72	3.199	81.25	2.225	56.52	2.955	75.06

PANEL CUTOUT FOR 792-011



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed



792-011

Panel Plug, 90° PC Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Socket contacts



PCB FOOTPRINTS FOR 792-011 CONNECTOR

⚠ Optimizing PCB Design


See Glenair Application Note AN0002 *Design and Installation of El Ochito PCB Connectors* for recommended solder pad sizing, trace routing, and connector installation.
<https://cdn.glenair.com/test-reports-and-technical-information/pdf/application-note/an0002.pdf>

⚠ PCB hole patterns are shown for the **component mounting side** of the circuit board, looking through the connector.


Detail B




A-1P1 A-1G1




A-3P1




B-2P2 B-2G2




B-6P2




B-23P1



C-3P3 C-3G3



C-9P3



C-24P2

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed




792-011


Panel Plug, 90° PC Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Socket contacts


PCB FOOTPRINTS FOR 792-011 CONNECTOR




D-12P4




D-4P4 D-4G4




D-27P3



E-5P5 E-5G5



E-15P5



E-45P3

SERIES 792 HIGH-SPEED