

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay



793-001

Plug, Panel Mount, Horizontal, Crimp

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ Crimp termination




Dual bay blind mating. Space-saving 793-001 connector features high-density, high current and high frequency capabilities, saves size and weight compared to legacy rack-and-panel types. Connector has two inserts. Machined shell has groove for attaching backshell 799-015. Size 23 contacts are included with connector; power contacts (#8, #12 or #16) or coaxial RF contacts (#12 and #16) are ordered separately. Pin contacts are recessed to protect them from damage. Connectors become non-scoop proof at parallel horizontal angles of entry from 16°–47°.


- Aerospace-grade high-density rack-and-panel connector
- Dual bay horizontal
- Environmental
- M39029-type crimp, rear-release contacts

INSERT ARRANGEMENTS

Identification numbers are mating face of plug (socket) connector




102
102 #23 Contacts



4W4
4 #8 Contacts




17W17
17 #16 Contacts



68W2
66 #23, 2 #12 Contacts




40W4
36 #23, 4 #12 Contacts



74W4
70 #23, 4 #16 Contacts



7W7
7 #12 Contacts




19W6
13 #23, 6 #12 Contacts


HOW TO ORDER

Sample Part Number	793-001S	A17W17	B102	M	G	B
Basic Part Number	793-001S Plug, Socket Contacts					
Bay "A" Insert Arr.	A102 A4W4 A17W17	A68W2 A40W4 A7W7 A19W6	A7W7			
Bay "B" Insert Arr.		B102 B4W4 B17W17	B68W2 B40W4 B7W7 B19W6	B7W7		
Shell Finish			M Electroless Nickel MT Nickel / PTFE NF Olive Drab Cadmium TZ Tin-Zinc ZR Black Zinc-Nickel			
Hardware Option Table 1			P Female Jackposts G Guide Pins For blind mating B Guide Bushings For blind mating			
Polarization Key Option	Enter Letter Designator for Position A , B , C , or D per Mod Code 1502 (see page D-5 for details) Omit for none					


TABLE 1 HARDWARE OPTION



P Female Jackpost



G Guide Pin



B Guide Bushing

RATINGS

- Voltage (DWV): size 23 contacts 750 VAC, Size 8, 12 and 16: 1800 VAC
- Current: #23 5A, #16 13A, #12 23A, #8 46A
- Operating temperature: -65 to +150 °C
- Durability: 500 mating cycles
- Shock: 300 g
- Vibration: 20 g random
- Altitude immersion: 75,000 feet
- Ingress protection: IP67

CONSTRUCTION

- Contacts: Copper alloy, gold over nickel finish
- Shell: Aluminum
- Insulators: High performance thermoplastic
- Wire grommet: Fluorosilicone/silicone blend
- Contact retaining clip: Beryllium copper, unplated
- Hardware: Stainless steel

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay



SERIES
793
Dual-Bay

793-001


Plug, Panel Mount, Horizontal, Crimp

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ Crimp termination

SERIES 793 DUAL-BAY



CRIMP CONTACTS			
	Contact Size	Socket Contact Part No.	AWG Wire Size
Size 23 contacts are included with connector. Size 16, 12, and 8 contacts are not included and are ordered separately. See "Contacts and Tools" section for crimp tool info and coaxial contact ordering information.	23	809-002	22 – 28
	16	857-448-16 (M39029/57-358)	16 – 20
	12	857-448-12 (M39029/57-359)	12 – 14
	8	850-138F	8



Use backshell part number 799-015 (Size M). Two backshells are required per connector. Two piece backshell has lip to lock into groove on connector. Available in top entry, side entry and 45° entry.

Series 793 Features and Insert Arrangements



Series 793 Dual-Bay

The Series 793 connector is a high reliability aerospace-grade rectangular connector with two inserts for up to 204 contacts. The 973 connector saves size and weight compared to legacy rack-and-panel types. The tight-tolerance scoop-proof shell and recessed contacts guarantee accurate alignment and trouble-free service. Contact sizes are #23, #16, #12, and #8 in eight insert arrangements.

Connector Types

Crimp, Rear Release

793 connectors have metal retention clips inside the contact cavities. Wired contacts snap into connector bodies and can be removed with a release tool. Size 23 contacts are included with connector. Other sizes are ordered separately.

PCB Termination

793 connectors are available in straight tail or 90° PCB versions. Connectors have factory-installed PCB terminals. Terminals are epoxy sealed and are compatible with conformal coatings.

Contact Sizes

Size 23 (#22 – #28 AWG wire)



Size 16 (#16 – #20 AWG wire)



Size 12 (#12 – #14 AWG wire)



Size 8 (#8 AWG wire)



Panel Mounting

Space-saving Series 793 connectors are designed for rear panel installation. Panel mounting holes have stainless steel #6-32 self-locking threaded inserts.


Environmental Protection

793 crimp connectors have fluorosilicone wire grommets and interfacial seals for ingress protection. PCB versions have epoxy-sealed terminals.


Horizontal or Vertical

793 connectors have two inserts arranged side-by-side or top-and-bottom:

Horizontal



Vertical



Blind Mating

Series 793 connectors have precision machined shells and guide pins for use in blind mate rack-and-panel applications.



EMI Shielding

Ground Springs

Optional ground springs provide low, stable shell-to-shell resistance. Available on 793 receptacles.

90° PCB Shroud

Right angle PCB connectors have a metal shroud over contact tails for EMI shielding.

EMI Backshell


Crimp connectors have grooves for attaching EMI backshells. Terminate cable shield to backshell with *BandMaster ATS*® band strap.



Hardware Options

Hardware options include guide pins, jackscrews or screwlocks.

Scoop-Proof Interface Series 793 pin contacts are recessed to protect them from damage. Connectors become non-scoop proof at parallel horizontal angles of entry from 16°–47°.




INSERT ARRANGEMENTS

Identification numbers are mating face of plug (socket) connector



102

102 #23 Contacts



4W4

4 #8 Contacts



17W17

17 #16 Contacts



68W2

66 #23, 2 #12 Contacts



40W4

36 #23, 4 #12 Contacts



74W4

70 #23, 4 #16 Contacts



7W7

7 #12 Contacts



19W6

13 #23, 6 #12 Contacts

Series 793 Material and Finish Options Polarization Keying Options

The Series 793 Dual-bay connector is available in five preferred finishes:

electroless nickel, nickel-PTFE, tin-zinc, cadmium, and zinc-nickel.

Additional material and finish options are available. Replace the preferred plating code with the alternate code from the table below.

TIN-ZINC PLATING

The United States Department of Defense (DOD) has mandated the elimination of cadmium from DOD weapons systems because of toxicity concerns. The European Union has also restricted the use of cadmium on electronics equipment (RoHS). Tin-Zinc is a RoHS cadmium-free sacrificial finish that offers high conductivity and shielding performance, corrosion resistance, solderability, and proven compatibility with legacy cadmium and zinc-nickel finishes. Tin-Zinc is DLA-qualified and RoHS compliant.

SERIES 79 PREFERRED FINISH OPTIONS					
	Electroless Nickel	Nickel-PTFE	Tin-Zinc	Olive Drab Cadmium	Black Zinc-Nickel
Glenair Code	M	MT	TZ	N	ZR
Corrosion Resistance	Fair	Excellent	Excellent	Excellent	Excellent
Temperature Range	-65 to +200 °C	-65 to +175 °C	-65 to +175 °C	-65 to +175 °C	-65 to +175 °C
Salt Spray Hours	48	500	500	500	500
Conductivity	Excellent	Excellent	Very Good	Very Good	Very Good
RoHS Compliant ⁽¹⁾	Yes	Yes	Yes	No	Yes

⁽¹⁾ Does not contain cadmium or hexavalent chromium. Meets EU requirements.

ALTERNATE SHELL MATERIAL AND FINISH CODES

Code	Shell Material	Shell Finish	Finish Specification	Salt Spray Hrs.	Electrical Conductivity	RoHS ⁽¹⁾
C	Alum	Anodize, Black	MIL-PRF-8625	48	Non-Conductive	✓
E⁽²⁾	Alum	Chem Film, Gold	MIL-DTL-5541	168	Conductive	
J	Alum	Cadmium, Yellow	AMS-QQ-P-416	500	Conductive	
Z1	SST	Passivate	AMS2700	500	Conductive	✓
Z2	Alum	Gold	MIL-DTL-45204	48	Conductive	✓
ZM	SST	Electroless Nickel	AMS-C-26074	500	Conductive	✓
ZMT	SST	Nickel-PTFE	AMS2454	1000	Conductive	✓
ZW	SST	Cadmium, Olive Drab	AMS-QQ-P-416	500	Conductive	
ZZR	SST	Zinc-Nickel, Black	ASTM B841	500	Conductive	✓


⁽¹⁾ Does not contain cadmium or hexavalent chromium. Meets EU requirements.

⁽²⁾ Maximum temperature = +125°C

OPTIONAL POLARIZATION KEYS

To prevent mis-mating of identical shell size and insert arrangement connectors

Series 793 connectors are available with an integral polarizing key. Keyed plug connectors have a raised boss on the shell. Receptacles have corresponding keyway. Add the keying position letter designator to the end of the part number to order. *Note: keyed receptacles will mate with unkeyed plugs.*



HOW TO ORDER					
Step 1	Create a Series 793 connector part number:				
Step 2	Add the keying position letter designator to the part number: A, B, C, or D (for horizontal connectors); or A, B, C, D, E, F, G, H, J, K, or L (for vertical connectors)				
	793-001SA17W17B102MG				
	793-001SA17W17B102MGB				

POLARIZING KEY LOCATIONS - HORIZONTAL CONNECTORS

All horizontal connector polarizing keys are on the centerline, as shown in the diagram.

POLARIZING KEY LOCATIONS - VERTICAL CONNECTORS											
Key Position Offset From Vertical Centerline											
Position A		Position B		Position C		Position D		Position E		Position F	
in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003
.550	13.97	0.000	0.00	.550	13.97	.600	15.24	0.000	0.00	.600	15.24
Position G		Position H		Position J		Position K		Position L		Position M	
in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003
0.315	8.00	0.315	8.00	0.350	8.89	0.350	8.89	0.475	12.07	0.475	12.07

Specifications

CONSTRUCTION

Contacts	Copper alloy, gold over nickel finish
Hood, socket contact	Stainless steel, passivated
Clip, contact retaining	Beryllium copper
Clip, insert retaining	Beryllium copper
Insulators	High performance thermoplastic
Grommet and face seal	Fluorosilicone/silicone blend
Shell	Aluminum
Interfacial Seal	Fluorosilicone/silicone blend
EMI spring	Beryllium copper, electroless nickel plated
EMI shroud (90° PCB)	Aluminum
Encapsulant (PCB)	Epoxy
Hardware	Stainless steel, passivated

RATINGS

Voltage (DWV)	Size 23 contacts: 750 VAC Size 8, 12 and 16 contacts: 1800 VAC										
Current Rating	<table border="1"> <thead> <tr> <th>Contact Size</th> <th>Current (A)</th> </tr> </thead> <tbody> <tr> <td>#23</td> <td>5</td> </tr> <tr> <td>#16</td> <td>13</td> </tr> <tr> <td>#12</td> <td>23</td> </tr> <tr> <td>#8</td> <td>46</td> </tr> </tbody> </table>	Contact Size	Current (A)	#23	5	#16	13	#12	23	#8	46
Contact Size	Current (A)										
#23	5										
#16	13										
#12	23										
#8	46										
Operating Temperature	-65 to +150 °C										
Ingress Protection	IP67										
Durability	500 mating cycles										

PRODUCT SPECIFICATIONS

Description	Requirement	Procedure
Contact Resistance	SAE AS39029 Table V	EIA-364-06
Low Level Contact Resistance	SAE AS39029 Table IV	EIA-364-23
Insulation Resistance	5000 megohms minimum	EIA-364-21
Dielectric Withstanding Voltage	#23 contacts 750 volts, #8, 12 & 16 contacts 1800 volts	EIA-364-20
Current Rating	#23: 5A, #16: 13A, #12: 23A, #8: 46A	EIA-364-70 Method 1
Shell-to-shell Resistance	2.5 millivolt drop maximum (connector with EMI spring)	EIA-364-83
Shielding Effectiveness	100 – 1000MHz: >75 dB, 1 – 4GHz: >60dB, 4 – 10GHz: >40dB	EIA-364-66
Ingress Protection	IP67 rating	IEC-60529
Vibration, Sine	20 g	EIA-364-28 Test Condition IV
Vibration, Random	16.91 g rms	EIA-364-28 Test Condition VI Letter J
Mechanical Shock	300 g	EIA-364-27 Condition D
Thermal Shock	-65 to +150 °C	EIA-364-32 Test Condition IV,
Humidity	10 Day, +25 to +65° C	EIA-364-31 Method IV, Step 7b vibration deleted.
Mechanical Durability	500 mating cycles	EIA-364-09
Salt Spray	Plating code M: 48 hours, MT, ZR, N, TZ: 500 hours	EIA-364-26
Solderability, PC Tail Contacts	95% solder coverage. Smooth, bright and even finish.	EIA-364-52 Category 3, 8 hours steam aging
Resistance To Soldering Heat	260° C, 10 seconds	EIA-364-56
Fluid Immersion	No damage from immersion in various fuels and oils.	EIA-364-10
Altitude Immersion	75,000 feet	EIA-364-03
Contact Retention	MIL-DTL-38999 Table XVIII	EIA-364-29
Contact Separation Force	SAE AS39029 Table 9	EIA-364-37
Magnetic Permeability	2 μ maximum	EIA-364-54