

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay



793-009

Plug, Panel Mount, Horizontal, 90° PCB Tails

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ 90° PCB tails




Dual bay, blind mating, PC tails.

Space-saving 793-009 connector features high-density and high current capabilities, saves size and weight compared to legacy rack-and-panel types. Connector has factory-installed 90° PC tail contacts. PC tails are encapsulated with epoxy potting compound. Mounting holes have self-locking threaded inserts for easy rear panel attachment. Connector has metal EMI cover over right angle PC terminals. Connectors become non-scoop proof at parallel horizontal angles of entry from 16°–47°.

- Aerospace-grade rectangular rack-and-panel receptacle connector
- Dual bay horizontal with 90° PC terminals
- Environmental
- Socket contacts


INSERT ARRANGEMENTS

Identification numbers are mating face of plug (socket) connector



102

102 #23 Contacts




4W4

4 #8 Contacts




17W17

17 #16 Contacts




68W2

66 #23, 2 #12 Contacts




40W4

36 #23, 4 #12 Contacts




74W4

70 #23, 4 #16 Contacts



7W7

7 #12 Contacts



19W6

13 #23, 6 #12 Contacts

HOW TO ORDER

Sample Part Number

793-009S

A17P17

B102

M

G

A

B

Basic Part Number

793-009S

Plug, Socket Contacts

Bay "A" Insert Arr.

A102

A68P2

A7P7

A4P4

A40P4

A19P6

A17P17

A74P4

Bay "B" Insert Arr.

B102

B68P2

B7P7

B4P4

B40P4

B19P6

B17P17

B74P4

Shell Finish

M Electroless Nickel

MT Nickel / PTFE

NF Olive Drab Cadmium

TZ Tin-Zinc

ZR Black Zinc-Nickel

Hardware Option Table 1

P Female Jackposts

G Guide Pins For blind mating

B Guide Bushings For blind mating

PC Tail Length


A .125 (3.2)

B .250 (6.4)


Polarization Key Option

Enter Letter Designator for Position **A, B, C,** or **D** per Mod Code 1502 (see page D-5 for details) **Omit** for none


TABLE 1 HARDWARE OPTION



P Female Jackpost



G Guide Pin



B Guide Bushing

RATINGS

- Voltage (DWV): size 23 contacts 750 VAC, size 8, 12 and 16: 1800 VAC
- Current: #23 5A, #16 13A, #12 23A, #8 46A
- Operating temperature: -65 to +150 °C
- Durability: 500 mating cycles
- Shock: 300 g
- Vibration: 20 g random
- Altitude immersion: 75,000 feet
- Ingress protection: IP67

CONSTRUCTION

- Contacts: Copper alloy, gold over nickel finish
- Shell: Aluminum
- EMI shroud: Aluminum
- Insulators: High performance thermoplastic
- Face seal: Fluorosilicone/silicone blend
- Hardware: Stainless steel
- Encapsulant: Epoxy

MICRO-CRIMP RECTANGULAR CONNECTORS


Series 793 Dual-Bay



793-009


Plug, Panel Mount, Horizontal, 90° PCB Tails

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ 90° PCB tails



SERIES 793 DUAL-BAY


PANEL CUTOUT FOR REAR MOUNTING



Application Note

Polarization Key Positions

See Mod Code 1502 pg. D-5 for details



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay


SERIES
793
Dual-Bay

793-009









Plug, Panel Mount, Horizontal, 90° PCB Tails

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ 90° PCB tails

PCB FOOTPRINTS FOR 793-009 CONNECTOR



PCB hole patterns below are shown for the **connector mounting side** of the circuit board.



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay



Series 793 Features and Insert Arrangements

SERIES 793 DUAL-BAY



Series 793 Dual-Bay

The Series 793 connector is a high reliability aerospace-grade rectangular connector with two inserts for up to 204 contacts. The 793 connector saves size and weight compared to legacy rack-and-panel types. The tight-tolerance scoop-proof shell and recessed contacts guarantee accurate alignment and trouble-free service. Contact sizes are #23, #16, #12, and #8 in eight insert arrangements.

Connector Types

Crimp, Rear Release


793 connectors have metal retention clips inside the contact cavities. Wired contacts snap into connector bodies and can be removed with a release tool. Size 23 contacts are included with connector. Other sizes are ordered separately.

PCB Termination

793 connectors are available in straight tail or 90° PCB versions. Connectors have factory-installed PCB terminals. Terminals are epoxy sealed and are compatible with conformal coatings.

Contact Sizes

Size 23 (#22 – #28 AWG wire)
Size 16 (#16 – #20 AWG wire)
Size 12 (#12 – #14 AWG wire)
Size 8 (#8 AWG wire)



Panel Mounting

Space-saving Series 793 connectors are designed for rear panel installation. Panel mounting holes have stainless steel #6-32 self-locking threaded inserts.


Environmental Protection

793 crimp connectors have fluorosilicone wire grommets and interfacial seals for ingress protection. PCB versions have epoxy-sealed terminals.


Horizontal or Vertical

793 connectors have two inserts arranged side-by-side or top-and-bottom:

Horizontal




Vertical



Blind Mating

Series 793 connectors have precision machined shells and guide pins for use in blind mate rack-and-panel applications.



EMI Shielding

Ground Springs

Optional ground springs provide low, stable shell-to-shell resistance. Available on 793 receptacles.

90° PCB Shroud

Right angle PCB connectors have a metal shroud over contact tails for EMI shielding.

EMI Backshell


Crimp connectors have grooves for attaching EMI backshells. Terminate cable shield to backshell with **BandMaster ATS**® band strap.



Hardware Options

Hardware options include guide pins, jackscrews or screwlocks.

Scoop-Proof Interface Series 793 pin contacts are recessed to protect them from damage. Connectors become non-scoop proof at parallel horizontal angles of entry from 16°–47°.




INSERT ARRANGEMENTS

Identification numbers are mating face of plug (socket) connector




102

102 #23 Contacts



4W4

4 #8 Contacts




17W17

17 #16 Contacts



68W2

66 #23, 2 #12 Contacts




40W4

36 #23, 4 #12 Contacts




74W4

70 #23, 4 #16 Contacts



7W7

7 #12 Contacts



19W6

13 #23, 6 #12 Contacts

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay

SERIES
793
Dual-Bay

Series 793 Material and Finish Options

Polarization Keying Options

SERIES 793 DUAL-BAY

The Series 793 Dual-bay connector is available in five preferred finishes:

electroless nickel, nickel-PTFE, tin-zinc, cadmium, and zinc-nickel.

Additional material and finish options are available. Replace the preferred plating code with the alternate code from the table below.

TIN-ZINC PLATING

The United States Department of Defense (DOD) has mandated the elimination of cadmium from DOD weapons systems because of toxicity concerns. The European Union has also restricted the use of cadmium on electronics equipment (RoHS). Tin-Zinc is a RoHS cadmium-free sacrificial finish that offers high conductivity and shielding performance, corrosion resistance, solderability, and proven compatibility with legacy cadmium and zinc-nickel finishes. Tin-Zinc is DLA-qualified and RoHS compliant.

SERIES 79 PREFERRED FINISH OPTIONS

	Electroless Nickel	Nickel-PTFE	Tin-Zinc	Olive Drab Cadmium	Black Zinc-Nickel
Glenair Code	M	MT	TZ	N	ZR
Corrosion Resistance	Fair	Excellent	Excellent	Excellent	Excellent
Temperature Range	-65 to +200 °C	-65 to +175 °C	-65 to +175 °C	-65 to +175 °C	-65 to +175 °C
Salt Spray Hours	48	500	500	500	500
Conductivity	Excellent	Excellent	Very Good	Very Good	Very Good
RoHS Compliant ⁽¹⁾	Yes	Yes	Yes	No	Yes

⁽¹⁾ Does not contain cadmium or hexavalent chromium. Meets EU requirements.

ALTERNATE SHELL MATERIAL AND FINISH CODES

Code	Shell Material	Shell Finish	Finish Specification	Salt Spray Hrs.	Electrical Conductivity	RoHS ⁽¹⁾
C	Alum	Anodize, Black	MIL-PRF-8625	48	Non-Conductive	✓
E⁽²⁾	Alum	Chem Film, Gold	MIL-DTL-5541	168	Conductive	
J	Alum	Cadmium, Yellow	AMS-QQ-P-416	500	Conductive	
Z1	SST	Passivate	AMS2700	500	Conductive	✓
Z2	Alum	Gold	MIL-DTL-45204	48	Conductive	✓
ZM	SST	Electroless Nickel	AMS-C-26074	500	Conductive	✓
ZMT	SST	Nickel-PTFE	AMS2454	1000	Conductive	✓
ZW	SST	Cadmium, Olive Drab	AMS-QQ-P-416	500	Conductive	
ZZR	SST	Zinc-Nickel, Black	ASTM B841	500	Conductive	✓

⁽¹⁾ Does not contain cadmium or hexavalent chromium. Meets EU requirements.


⁽²⁾ Maximum temperature = +125°C

OPTIONAL POLARIZATION KEYS

To prevent mis-mating of identical shell size and insert arrangement connectors

Series 793 connectors are available with an integral polarizing key. Keyed plug connectors have a raised boss on the shell. Receptacles have corresponding keyway. Add the keying position letter designator to the end of the part number to order. **Note: keyed receptacles will mate with unkeyed plugs.**

MOD-1502 KEY LOCATIONS



HOW TO ORDER

Step 1	Create a Series 793 connector part number:	793-001SA17W17B102MG
Step 2	Add the keying position letter designator to the part number: A, B, C, or D (for horizontal connectors); or A, B, C, D, E, F, G, H, J, K, or L (for vertical connectors)	793-001SA17W17B102MGB

POLARIZING KEY LOCATIONS - HORIZONTAL CONNECTORS

All horizontal connector polarizing keys are on the centerline, as shown in the diagram.

POLARIZING KEY LOCATIONS - VERTICAL CONNECTORS

Key Position Offset From Vertical Centerline											
Position A		Position B		Position C		Position D		Position E		Position F	
in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003
.550	13.97	0.000	0.00	.550	13.97	.600	15.24	0.000	0.00	.600	15.24
Position G		Position H		Position J		Position K		Position L		Position M	
in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003	in±.001	mm±.003
0.315	8.00	0.315	8.00	0.350	8.89	0.350	8.89	0.475	12.07	0.475	12.07

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay



Specifications

SERIES 793 DUAL-BAY

CONSTRUCTION

Contacts	Copper alloy, gold over nickel finish
Hood, socket contact	Stainless steel, passivated
Clip, contact retaining	Beryllium copper
Clip, insert retaining	Beryllium copper
Insulators	High performance thermoplastic
Grommet and face seal	Fluorosilicone/silicone blend
Shell	Aluminum
Interfacial Seal	Fluorosilicone/silicone blend
EMI spring	Beryllium copper, electroless nickel plated
EMI shroud (90° PCB)	Aluminum
Encapsulant (PCB)	Epoxy
Hardware	Stainless steel, passivated

RATINGS

Voltage (DWV)	Size 23 contacts: 750 VAC Size 8, 12 and 16 contacts: 1800 VAC	
Current Rating	Contact Size	Current (A)
	#23	5
	#16	13
	#12	23
	#8	46
Operating Temperature	-65 to +150 °C	
Ingress Protection	IP67	
Durability	500 mating cycles	

PRODUCT SPECIFICATIONS

Description	Requirement	Procedure
Contact Resistance	SAE AS39029 Table V	EIA-364-06
Low Level Contact Resistance	SAE AS39029 Table IV	EIA-364-23
Insulation Resistance	5000 megohms minimum	EIA-364-21
Dielectric Withstanding Voltage	#23 contacts 750 volts, #8, 12 & 16 contacts 1800 volts	EIA-364-20
Current Rating	#23: 5A, #16: 13A, #12: 23A, #8: 46A	EIA-364-70 Method 1
Shell-to-shell Resistance	2.5 millivolt drop maximum (connector with EMI spring)	EIA-364-83
Shielding Effectiveness	100 – 1000MHz: >75 dB, 1 – 4GHz: >60dB, 4 – 10GHz: >40dB	EIA-364-66
Ingress Protection	IP67 rating	IEC-60529
Vibration, Sine	20 g	EIA-364-28 Test Condition IV
Vibration, Random	16.91 g rms	EIA-364-28 Test Condition VI Letter J
Mechanical Shock	300 g	EIA-364-27 Condition D
Thermal Shock	-65 to +150 °C	EIA-364-32 Test Condition IV,
Humidity	10 Day, +25 to +65° C	EIA-364-31 Method IV, Step 7b vibration deleted.
Mechanical Durability	500 mating cycles	EIA-364-09
Salt Spray	Plating code M: 48 hours, MT, ZR, N, TZ: 500 hours	EIA-364-26
Solderability, PC Tail Contacts	95% solder coverage. Smooth, bright and even finish.	EIA-364-52 Category 3, 8 hours steam aging
Resistance To Soldering Heat	260° C, 10 seconds	EIA-364-56
Fluid Immersion	No damage from immersion in various fuels and oils.	EIA-364-10
Altitude Immersion	75,000 feet	EIA-364-03
Contact Retention	MIL-DTL-38999 Table XVIII	EIA-364-29
Contact Separation Force	SAE AS39029 Table 9	EIA-364-37
Magnetic Permeability	2 μ maximum	EIA-364-54