

M28840/24 Mounting Gasket for use with MIL-PRF-28876 Connectors  
MS3186 Jam Nut with Safety Wire Holes

NAVSEA / Underwater Fiber Optics

HOW TO ORDER			
Sample Part Number	M28840/24	J	A
Basic Number	Mounting Gasket		
Shell Size	See Dimensions table		
Material and Finish Designator	A = Fluorosilicone B = EMI, silicone		

DIMENSIONS					
	Designator	A	B Dia	C	D Dia
	A (11)	.760 (19.30)	.766 (19.46)	1.039 (26.39)	.130 (3.30) .110 (2.79)
		.740 (18.80)	.750 (19.05)	1.023 (25.98)	
	B (13)	.853 (21.67)	.891 (22.63)	1.154 (29.31)	
		.833 (21.16)	.875 (22.22)	1.138 (28.90)	
C (15)	.978 (24.84)	1.078 (27.38)	1.274 (32.36)		
	.958 (24.33)	1.062 (26.97)	1.258 (31.95)		
F (23)	1.291 (32.79)	1.516 (38.51)	1.734 (44.04)		
	1.271 (32.28)	1.500 (38.10)	1.718 (43.64)		

HOW TO ORDER			
Sample Part Number	MS3186	A	-113 B
Basic Number	Jam Nut with Safety Wire Holes		
Material	A = Aluminum S = Steel C = CRES		
Dash Number	See MS3186 Spec		
Finish	See Finish table		

**NOTES**

- Assembly identified with manufacturer's name and part number, space permitting.
- For complete dimensions, see the MIL-Spec for dash numbers and associated dimensions.
- Metric dimensions (mm) are in parentheses.

FINISH	
Code	Finish Description
A	Black Anodize (Material 'A' only)
B	Black Cadmium over Corrosion Resistant Steel (Material 'C' only)
C	Clear Cadmium (Material 'A' only)
E	Electrodeposited Nickel
N	Electroless Nickel (Space Use Only)
P	Passivated (Material 'C' only)
T	Tin Plate (Material 'S' only)
W	1,000 Hour Cadmium Olive Drab over Electroless Nickel

