

OPTIMIZED
FOR USE WITH
MIL-STAR
HIGH-PERFORMANCE HOOKUP WIRE AND CABLE

GateLink Pro™

GateLink Pro™
high-speed data
uplink connector



Environmentally-sealed breakaway design for high- speed data transfer between terminal gate and aircraft

GateLink Pro™ connectors are exactly designed to meet the needs of airport terminal-to-aircraft data uplinks. The IP68 sealed receptacle connector on the aircraft is designed for low profile environmental performance (available ProSeal™ protective cover adds additional environmental protection). Plug connectors are ruggedized for rough handling with pogo pin contacts and retention springs recessed deep into the plug to prevent damage. Designed for fast and reliable high-speed Ethernet data transfer up to 1Gb / second. Turnkey overmolded cable assemblies as well as discrete connectors and environmental shrink boots are available.



- Durable pogo pin contact system rated to tens of thousands mating cycles
- Sealed receptacle available with ProSeal spring-action protective cover
- Straight or right-angle Autoshrink wire protection boots or rugged overmolded plug assemblies for reliable environmental protection

IP68 SEALED GateLink Pro™



High-speed data uplink connector

GATELINK PRO APPLICATIONS AND SOLUTIONS

Wired datalink interconnect access to the aircraft from the airline terminal gate supports various information domains and data types including aircraft traffic control, airline information services, passenger entertainment, weather, and so on. Airline operating center applications (flight plans, schedules, advisories) are quickly and reliably uploaded to the aircraft during turnarounds at the gate. Mechanical and environmental damage to the datalink interface is a common problem solved by GateLink Pro.



Overmolded environmental plugs and hybrid GateLink Pro to RJ45 cable sets



IP68 sealed receptacle with integrated ProSeal™ protective cover and Autoshrink™ environmental sealing / strain relief boot.



Mated GateLink Pro™ plug and receptacle cordsets with shielded twisted pair cabling. Plug side features environmental overmolding, receptacles side utilizes strain relief boot

GATELINK PRO SPECIFICATIONS



Voltage rating	500 VAC
Current rating	5 amps
Contact resistance	20 milliohms maximum
Plug-to-receptacle ground resistance	<5 milliohm
Maximum wire size	#24 AWG
Insulation resistance	5000 megohms min.
Water immersion	MIL-STD-810 Method 512, one meter for one hour
Durability	2000 mating cycles (receptacle)
Corrosion resistance	1000 hours
Sine vibration	EIA-364-28 condition IV, 20g peak
Random vibration	EIA-364-28 condition V letter H, 29g rms
Shock	EIA-364-27 condition D, 300g peak
EMI shielding effectiveness	40 dB minimum to 10 GHz


GATELINK PRO AVAILABLE ACCESSORIES



Anti-vibration and shock spring-action solution • Self-aligning environmental seals



Autoshrink is a high-performance elastomeric material (Glenair Duralectric™ formula polymer GPS67) cold-action shrink boot and jacket solution for commercial aerospace electrical wire interconnect systems



G
H
I
J
K
L
M
N
O
P
Q
R
S
T
U
V
W
X
Y
Z