



189-116 NGCON MIL-PRF-64266/10 Style Receptacle Dust Cover

MATERIAL AND FINISH

- Dust Cover: See Table I
- Lanyard: Stainless Steel/Teflon Coated
- Rivet: Stainless Steel/Passivate
- Fastner: Stainless Steel/Passivate
- Ring: Stainless Steel/Passivate
- Gasket: Fluorosilicone

NOTES

- Dust cover designed in accordance with the requirements of MIL-PRF-64266/11.
- For mating connector, see Glenair drawing 180-118.

MATERIAL AND FINISH		
Code	Material	Finish
GB4	Aluminum Alloy	Anodize, Black
ME		Electroless Nickel
MN		Mega-Nickel
MT		Nickel-Ptfe, Grey
NF		Cadmium, Olive Drab
TZ		Tin-Zinc
ZN		Zinc-Nickel, Olive Drab
ZR	Stainless Steel	Zinc-Nickel, Black
ZI		Passivate
ZL		Electro-Deposited Nickel

HOW TO ORDER						
Sample Part Number	189-116	ME	-15	F	1	-6
Basic Number	NGCON MIL-PRF-64266/10 Style Receptacle Dust Cover					
Material/Finish	See Material and Finish table					
Shell Size	See Shell Size / Dimensions / Peek Conduit Size table					
Lanyard Style	F = Teflon Coated Stainless Steel					
Lanyard Attachment	1 = Fastner 2 = Ring					
Lanyard Length	5" Minimum (L) In Inches					

SHELL SIZE / DIMENSIONS

Shell Size	T Thread Class 2A	øA Max	øB	øC
11	.750-.1P-.2L-DS	1.028 (26.11)	.900 (22.86) .880 (22.35)	1.800 (45.72)
13	.875-.1P-.2L-DS	1.141 (28.98)	1.025 (26.03) 1.005 (25.53)	1.950 (49.53)
15	1.062-.1P-.2L-DS	1.263 (32.08)	1.215 (30.86) 1.195 (30.35)	2.050 (52.07)
23	1.500-.1P-.2L-DS	1.705 (43.26)	1.650 (41.91) 1.630 (41.40)	2.690 (68.33)