


**FA00861**  
**ARINC801 Fiber Optic Test Probe**  
**Non-Keyed Jumper Assembly**



**Fiber optic test probe for fast and easy optical analysis of installed fiber optic systems**


**How To Order**



Symbol	Size
<b>A</b>	MM 100/140
<b>B</b>	MM 62.5/125
<b>C</b>	MM 50/125
<b>D</b>	MM 200/230
<b>E</b>	SM 9.3/125
<b>F</b>	SM 5.8/125
<b>G</b>	SM 7.5/125

Optical insertion loss  $\leq 0.5$  dB @  
 850 or 1310 nm wavelength.  
 Glenair Fiber Optic Test Probe U.S.  
 Patent Number 5,960,137.

**Connector Type:**  
**A** = ST Connector  
**B** = FC Connector  
**C** = SC Connector  
**D** = LC Connector  
**E** = FC/APC Connector  
**F** = SC/APC Connector  
**G** = LC/APC Connector



Length	Tolerance
1 meter	$\pm 1.00$ (25.4)
2 to 3 meters	$\pm 3.00$ (76.2)
4 to 6 meters	$\pm 4.00$ (101.6)
7 to 10 meters	$\pm 6.00$ (152.4)


**Note**

- "PC" physical contact polish to be IAW Glenair manufacturing procedure AQS-A002-F
- For use with the following test probe adapters:  
 180-131: GHD (180-122)

**Fiber optic polishing tool for ARINC 801 style termini fiber optic test probes**



**How To Order**



**Note**

- Polishing puck is for PC polish only. For APC Glenair recommends autopolish, consult factory for more information
- Polishing tool is designed for use with the following Glenair termini:  
 181-047 (Pin, size 18 terminus)  
 181-056 (Pin, size 18 terminus)