



189-115 NGCON MIL-PRF-64266/10 Style Plug Dust Cover

HOW TO ORDER						
Sample Part Number	189-115	ME	-15	F	2	-6
Basic Number	NGCON MIL-PRF-64266/10 Style Plug Dust Cover					
Material/Finish	See Material and Finish table					
Shell Size	See Shell Size / Dimensions / Peek Conduit Size table					
Lanyard Style	F = Teflon Coated Stainless Steel					
Lanyard Attachment	1 = Fastner 2 = Cable Loop 3 = Ring					
Lanyard Length	5" Minimum (L) In Inches					

MATERIAL AND FINISH

- Dust Cover: See Table I
- Lanyard: Stainless Steel/Teflon Coated
- Rivet: Stainless Steel/Passivate
- Fastner: Stainless Steel/Passivate
- Ring: Stainless Steel/Passivate
- Gasket: Fluorosilicone

NOTES

- Dust cover designed in accordance with the requirements of MIL-PRF-64266/10.
- For mating connector, see Glenair drawing 180-118.

SHELL SIZE / DIMENSIONS								
Shell Size	T Thread Class 2A	øA Max	øB	øC	øD	øF Min	øG	H Max
11	.750-.1P-.2L-DS	1.028 (26.11)	.581 (14.75) .569 (14.45)			.709 (18.0) .606 (15.4)	.608 (17.30) .578 (14.70)	1.5 (38.1)
13	.875-.1P-.2L-DS	1.141 (28.98)	.705 (17.90) .693 (17.60)	.125 (3.17) .110 (2.79)	.210 (5.44) .170 (4.32)	.787 (20.0) .733 (18.6)	.773 (19.60) .703 (17.90)	1.7 (43.2)
15	1.062-.1P-.2L-DS	1.263 (32.08)	.877 (22.27) .865 (21.97)			.906 (23.0) .890 (22.6)	.905 (24.10) .875 (22.20)	1.8 (45.7)
23	1.500-.1P-.2L-DS	1.705 (43.26)	1.299 (32.99) 1.287 (32.69)	.173 (3.87) .152 (3.48)	.280 (7.11) .240 (.610)	1.339 (34.0) 1.330 (33.8)	1.358 (34.50) 1.328 (33.70)	2.3 (58.4)

MATERIAL AND FINISH		
Code	Material	Finish
GB4	Aluminum Alloy	Anodize, Black
ME		Electroless Nickel
MN		Mega-Nickel
MT		Nickel-Ptfe, Grey
NF		Cadmium, Olive Drab
TZ		Tin-Zinc
ZN		Zinc-Nickel, Olive Drab
ZR		Zinc-Nickel, Black
ZI	Stainless Steel	Passivate
ZL		Electro-Deposited Nickel