


PF0-0001 Optical flex assembly, straight, loopback, or curve, with I/O connector options




HOW TO ORDER						
Sample Part Number	PF0-0001	-C	-01	-01	-09	-12
Basic Part Number	Optical Flex Jumper Assembly					
Shape	 L = Loopback S = Straight C = Curve					
	Must fit in 12" X 12" area. Consult Glenair for custom design					
Connector A	-01 = MT Ferrule -02 = SuperNine MT -03 = Series 79 MT		-04 = MPO -05 = VITA 66.1 -06 = VITA 66.4			
Connector B	-01 = MT Ferrule -02 = SuperNine MT -03 = Series 79 MT		-04 = MPO -05 = VITA 66.1 -06 = VITA 66.4			
Fiber Size	-09 = 9.3/12.5µm Singlemode -50 = 50/125µm Multimode -62 = 62.5/125µm Multimode		-09R = Radhard Singlemode -50R = Radhard Multimode -62R = Radhard Multimode			
Number of Fibers	-12					
Part numbering is for reference purposes only. A unique Glenair part number will be assigned.						




PF0-0001 Optical flex assembly, straight, loopback, or curve, with I/O connector options

EXAMPLE JUMPER ASSEMBLY, LOOPBACK SHAPE, SUPERNINE MT CONNECTOR



PF0-00001-L-02-09-12 (For Reference)

EXAMPLE JUMPER ASSEMBLY, STRAIGHT SHAPE, SERIES 79 MT AND MPO CONNECTORS



PF0-00001-S-03-04-50-12 (For Reference)