





947-120
Jam Nut Mount Hermetic Bulkhead Feed-Thru
.062/.125ⁱⁿ Panel
MIL-DTL-38999 Series II Type

B



Dimensions in Inches (millimeters) are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324


Printed in U.S.A.

947-120
Jam Nut Mount Hermetic Bulkhead Feed-Thru
.062/.125ⁱⁿ Panel
MIL-DTL-38999 Series II Type



TABLE I: CONNECTOR DIMENSIONS

SHELL SIZE	A THREAD CLASS 2A	B DIA MAX	C HEX	D FLATS	E DIA ±.005(0.1)	F +.000-.005 (0-0.1)
08	.875-20 UNEF	.474(12.0)	1.062(27.0)	1.250(31.8)	.885(22.48)	.830(21.1)
10	1.000-20 UNEF	.591(15.0)	1.188(30.2)	1.375(34.9)	1.010(25.65)	.955(24.3)
12	1.125-18 UNEF	.751(19.1)	1.312(33.3)	1.500(38.1)	1.135(28.83)	1.085(27.6)
14	1.250-18 UNEF	.876(22.3)	1.438(36.5)	1.625(41.3)	1.260(32.01)	1.210(30.7)
16	1.375-18 UNEF	1.001(25.4)	1.562(39.7)	1.781(45.2)	1.385(35.18)	1.335(33.9)
18	1.500-18 UNEF	1.126(28.6)	1.688(42.9)	1.890(48.0)	1.510(38.35)	1.460(37.1)
20	1.625-18 UNEF	1.251(31.8)	1.812(46.0)	2.016(51.2)	1.635(41.53)	1.585(40.3)
22	1.750-18 UNS	1.376(35.0)	2.000(50.8)	2.140(54.4)	1.760(44.70)	1.710(43.4)
24	1.875-16 UN	1.501(38.1)	2.125(54.0)	2.265(57.5)	1.885(47.88)	1.835(46.6)



HERMETIC LEAK RATE MOD CODES

Designator	Required Leak Rate
-585A	1 x 10 ⁻¹⁰ cc Helium per second
-585B	1 x 10 ⁻⁹ cc Helium per second
-585C	1 x 10 ⁻⁸ cc Helium per second

APPLICATION NOTES

- | | |
|---|---|
| <ol style="list-style-type: none"> 1. Assembly identified with manufacturer's name and part number, space permitting. 2. For pin/pin or socket/socket, symmetrical layouts only consult factory for available insert arrangements). 3. Power to a given contact on one end will result in power to contact directly opposite, regardless of identification letter. 4. Hermeticity = less than 1 x 10⁻⁷ cc/sec at one atmosphere. | <ol style="list-style-type: none"> 5. Not for use in liquid atmosphere. 6. Material/Finish:
Shell, lock ring, jam nut, bayonet pins—stainless steel/passivate
Contacts—copper alloy/gold plate and alloy 52/gold plate
Insulators—high-grade rigid dielectric/N.A. and full glass
Seals - silicone/ N.A. 7. Metric Dimensions (mm) are indicated in parentheses. |
|---|---|

Dimensions in Inches (millimeters) are subject to change without notice.