



GRF05-0005

50 Ohm TNC Coax Connector

Hermetic • Bulkhead Feedthrough





**Product
Series**


GRF05-0005 - Z1

Finish

Z1 = Passivated
ZL = Nickel Plate



RECOMMENDED
MOUNTING HOLE



APPLICATION NOTES

1. Performance (per applicable MIL-PRF-5539/34:

- Frequency range: DC to 11 GHz
- Insertion loss: .5db max
- VSWR: 1.4:1 max, 0.5 to 11 GHz
- IR: 5000 megaOhms min
- DWV: 1500 VAC between center contact and outer body
- Operating temperature: -65°C to 165°C
- Hemeticity: < 1 x 10⁻⁷ cc/sec of helium at 1 atm. delta pressure

2. Material/Finish:

- Body, jam nut: CRES/ see part number development
- Center pin: Alloy 52/gold plated
- Socket contact: BeCu/gold plated
- O-ring: fluorosilicone
- Insulator: fused vitreous glass, PTFE

Dimensions in Inches (millimeters) are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com

N-8

E-Mail: sales@glenair.com

Rev. 10.26.23