

GRF05-0014
50 Ohm SMA/F-SMA-F Special Connector Adapter
Hermetic • Feed-Thru




Special
Connectors

**Product
Series**

GRF05-0014 - ZL

Finish

Z1 = Passivated
ZL = Nickel Plate



N

APPLICATION NOTES

1. Performance:

- Meet applicable mechanical and environmental requirements per MIL-PRF-39012/92.
- Nominal impedance: 50 Ohms
- Frequency range: 0 to 18 GHz
- Voltage rating: 335 VAC, sea level; 85 VAC, 70k feet.
- Operation temperature range: -65°C to +165°C
- Leak rate: 1×10^{-7} ccHe/s MAX, 1 ATM
- Connectors identified with manufacturer's name, part number, and date code space permitting.

2. Connector interface per MIL-STD-348, SMA, Socket contact

3. Material/Finish:

- Shells and plate: see part number development
- Center pin contact (glass sealed section) Ni alloy/gold plated
- Center socket contact (mating ends) copper alloy/gold plated
- Insulators: fused vitreous glass, high grade rigid dielectric / N.A.
- Jam nut, washer: SST / N.A.
- O-ring: fluorosilicone / N.A.

Dimensions in Inches (millimeters) are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com **N-17** **E-Mail: sales@glenair.com**

REV. 12.02.25