



CONTACTS

857-155 PC Tail, Socket, High-Durability AS39029/56 type



Use with SuperNine 233-211 PC-Tail Wall-Mount Receptacles

Part Number	Contact Size	ØA Max	ØB	ØC	ØD	ØE	ØF Min	G°
857-155-23	#23	.055	.028	.045 .040	.020 .018	.034 .030	—	
857-155-22	#22	.062	.031	.050 .044	.020 .018	.034 .030	.047	50° 44°
857-155-20	#20	.078	.0415	.070 .064	.030 .028	.050 .044	.053	47° 40°
857-155-16	#16	.113	.064	.106 .100	.040 .038	.086 .080	.084	47° 40°
857-155-12	#12	.161	.0955	.144 .140	.072 .070	.124 .118	.118	47° 40°



DETAIL-A

83H-85179-8

NOTES

1. Material/finish
Contact - Copper alloy / gold plated over nickel (selective plating acceptable)
2. Socket contacts shall meet or exceed the applicable dimensional, electrical, and mechanical requirements specified in SAE-AS39029/56 before and after 1500 durability cycles
3. Area indicated shall meet the solderability requirements of J-STD-002
4. Point at which a square-ended pin of the same basic diameter as a mating contact first engages the socket contact spring.