


280-108 combo cable socket connectors with standard mounting flange, integral banding platform and crimp termination



Combo HiPer-D® Combo-D connectors, with integral banding platform, feature size #20 signal contacts and size #8 power or coax contacts. **Size #8 contacts are ordered separately.** The HiPer-D® features a rugged machined aluminum shell and wire grommet for environmental protection. Size #20 contacts are packaged with connector. Terminate contacts with crimp tools purchased separately. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Fluorosilicone rear grommet meets IP67 immersion requirement. 1000 VAC, 7.5 Amps (#20), up to 40 Amps with size #8 power contacts.

B

How To Order							
Sample Part Number			280-108	S	4S37	ME	S
Basic Part Number	280-108						
Contact	S = Socket B = Less contacts						
Shell Size-Contact Arrangement	See Shell Size - Contact Arrangements Table						
Shell Finish	ME = Electroless Nickel Over Aluminum MT = Nickel Fluorocarbon Over Aluminum		Z1 = Passivated Stainless Steel ZM = Nickel Over Stainless JF - Yellow Chromate Over Cadmium				
Mating Hardware	N = No Hardware (ø.120 Through Hole) L = Low Profile Hex Head Captive Jackscrew S = Hex Head Captive Screwlock		P = Female Jackpost (for Cable Mounting Only) K = Slot Head Extended Jackscrew T = Slot Head Extended Captive Screwlock				

Shell Size	Contact Arrangements			
	Combo D Arrangement		Hiper D Arrangement	
	Layout	Contact Quantity	Layout	Quantity
1	-2P2	2#8	1S9	9 #20
	-5P1	4#20, 1#8	1H15	15#22
2	-3P3	3 #8	2S15	15#20
	-7P2	5#20, 2#8	2H26	26#22
3	-11P1	10#20, 1#8	3H44	44#22
	-5P5	5 #8		
	-9P4	5#20, 4#8		
	-13P3	10#20, 3#8		
4	-17P2	15#20, 2#8	4H62	62#22
	-21P1	20#20, 1#8		
	-8P8	8 #8		
	-13P6	7#20, 6#8		
	-17P5	12#20, 5#8		
5	-21PA4	17#20, 4#8	5S50	50#20
	-25P3	22#20, 3#8		
	-27P2	25#20, 2#8		
	-36P4	32#20, 4#8		
6	-43P2	41#20, 2#8	6H104	104#22
	-47P1	46#20, 1#8		


Mating Hardware	
N Thru-Hole No Hardware	P Female Jackpost
S Captive Screwlock, Hex Head	L Captive Jackscrew, Hex Head
K Slot-Head Extended Jackscrew	T Slot-Head Extended Captive Screwlock

Specifications	
Current Rating	#20 7.5 AMPS, #8 40 AMPS
Test Voltage	1000 VAC RMS
Insulation Resistance	5000 megohms minimum @ 500 VDC
Operating Temperature	-65° C. to +200° C.
Ingress Protection	IP 67
Shock	300 g.
Vibration, Random	43.92 g.
Dielectric Withstanding Voltage	1000 Volts

Materials and Finishes	
Shell	How to Order table
Contacts	Copper alloy/ gold over nickel
Inserts	Thermoset epoxy
Retention Clips	Copper alloy
Grommet, O-ring	Fluorosilicone/N.A.
Hardware	300 series stainless steel

280-108 combo cable socket connectors with standard mounting flange, integral banding platform and crimp termination

280-108 DIMENSIONS



Dimensions														
Shell Size	Insert Pattern	"A" ±.015		"B" ±.015		"C" ±.005		"D" ±.005		"E" ±.005		"F" ±.005		Contact P/N
		In.	mm.											
1	SD 9	1.213	30.81	0.494	12.55	0.984	24.99	.643	16.33	.311	7.90	.620	15.75	M39029/63-368
	HD 15													M39029/57-354
2	SD 15	1.541	39.14	0.494	12.55	1.312	33.32	.971	24.66	.311	7.90	.620	15.75	M39029/63-368
	HD 26													M39029/57-354
3	SD 25	2.088	53.04	0.494	12.55	1.852	47.04	1.511	38.38	.311	7.90	.620	15.75	M39029/63-368
	HD 44													M39029/57-354
4	SD 37	2.729	69.32	0.494	12.55	2.5	63.50	2.159	54.84	.311	7.90	.620	15.75	M39029/63-368
	HD 62													M39029/57-354
5	SD 50	2.635	66.93	0.605	15.37	2.406	61.11	2.064	52.43	.423	10.74	.730	18.54	M39029/63-368
	HD 78													M39029/57-354
6	HD 104	2.729	69.32	0.668	16.97	2.5	63.50	2.189	55.60	.486	12.34	.795	20.19	M39029/57-354

NOTES

- See [About Series 28 HiPer-D® Shell Plating Options](#) for additional shell material and finish options. Glenair offers the industry's widest selection of plating options with no minimum order quantities or setup charges.
- For panel cutouts, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
- Connectors are supplied with size #20 crimp contacts per M39029. Contacts are not installed. Refer to [HiPer-D® Contacts and Tools](#) section for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
- Size 8 contacts are ordered separately.** Refer to [HiPer-D® Contacts and Tools](#) section for contact ordering information, specifications, crimp tool information, and insertion/extraction tools.
- Combo HiPer-D® connectors meet the applicable requirements of MIL-DTL-24308 and are intermateable with standard non-environmental D Subminiature connectors with corresponding contact arrangements and type. **Size 8 contacts from other manufacturers cannot be installed in HiPer-D® connectors.**
- Additional electrical, mechanical and environmental specifications are listed in [HiPer-D® Product Specification](#).