


CONTACTS

857-153 PC Tail, Pin,
High-Durability AS39029/58 type



Use with SuperNine 233-209/-210 PC-Tail Wall-Mount Receptacles

Part Number	Contact Size	Connector Compatibility	ØA	ØB	ØC	ØD	ØE	ØF (Flat)	G Rad.
857-153-22	#22	233-209 / 233-210	.0305 .0295	.072 .068	.050 .044	.020 .018	.034 .030	.011 Max.	.015
857-153-20	#20	233-209 / 233-210	.041 .039	.111 .107	.070 .064	.030 .028	.050 .044	.015 Max.	.020
857-153-16	#16	233-209 / 233-210	.0635 .0615	.156 .152	.106 .100	.040 .038	.086 .080	.028 .012	.025 .020
857-153-12	#12	233-210	.095 .093	.211 .207	.144 .140	.072 .070	.124 .118	.060 .044	.025 .020



NOTES

1. Material/finish
Contact - Copper alloy / gold plated over nickel (selective plating acceptable)
2. Pin contacts shall meet or exceed the applicable dimensional, electrical, and mechanical requirements specified in SAE-AS39029/58 before and after 1500 durability cycles
3. Area indicated shall meet the solderability requirements of J-STD-002