

HIGH-VOLTAGE kV Seal™ Contact Assemblies

Rev. 06.04.25



GHV-004 kV Seal Size #8 22 kV contacts for Size #8 cavities in SuperNine, Mighty Mouse 801, 802, 805, and Series 79 connectors



KV SEAL CONTACT FEATURES

- 22 kVDC operating voltage
- Special-design size #16 copper contacts molded into size #8 dielectric bodies
- For drop-in use in size #8 cavities in SuperNine, Mighty Mouse Series 801, 802, and 805, and Series 79 rectangular connectors

PERFORMANCE SPECIFICATIONS

- IR: 5000 Megohms at 500 VDC
- DWV: 33 kVDC, 10uA max leakage current at sea level / ambient conditions
- Temperature: -55° to +125°
- Add Mod Code **1223**** to part number to include high-altitude DWV testing in final inspection


MATERIAL / FINISH

- Inner Contact, Pin/Socket - copper alloy / gold over nickel
- Inner Contact, Socket Hood - Stainless steel / passivate
- Contact Insulator Body - high-grade rigid dielectric
- kV Seal - fluorosilicone blend
- Wire Overmold - silicone blend
- Wire - fluoropolymer primary insulation (standard). Silicone-coated fluoropolymer available.
- Assemblies using option **T** etched wire packaged in UV-resistant bags

HOW TO ORDER					
Sample Part Number	GHV-004	-D	P	T	9 -36
Series	GHV-004 = kV Seal 22 kVDC High-Voltage Contact Assembly, Size #8D				
Contact Envelope / Wire Gauge	D = #16 AWG wire (See Table II)				
Contact Gender and Assembly Type	P = Pin (AS39029/58 type), with flying lead S = Socket (AS39029/56 type), with flying lead PP = Double-ended Pin assembly SS = Double-Ended Socket assembly PS = Double-ended Pin and Socket assembly				
Wire Finish	S = Silicone-Coated Fluoropolymer T = Continuously-Etched Fluoropolymer				
Wire Color Code	9 = White (per MIL-STD-681. Other colors available, consult factory.)				
Total Length	in inches (e.g. -36 = 36 inches) 12" minimum needed for testing				

TABLE II - CONTACT ENVELOPE / WIRE GAUGE PERFORMANCE					
Sym	Contact Envelope		Wire Gauge	Current Rating	OP Voltage Through 70K ft.
	Pin	Socket			
D	#8	#8	16	13	22 kVDC

OUTGASSING PROPERTIES – GLENAIR SIZE 12 KV SEAL HV CONTACT						
Material	Manufacturer	TML%	CVCM%	VWR	Data Ref.	
3145 Clear Silicone RTV	Dow Corning	0.15	<0.01	0.09	w/o 59566-6	
CF2-135 Primer	Nusil	4.22	<0.01	2.36	wo 79884	
FEP Wire insulation	Glenair	0.01	0	0	GSF31882	
Duraelectric Wire Coating 961-066-S-26-X	NuSil	0.16	0.06	0.03	GT-14-109	
Duraelectric K 50 duro silicone GPS146-M2-5	Glenair	0.25	0.07	0.08	wo TR73288	



KV SEAL™ CONTACT ASSEMBLIES