



Panel Cutout Dimensions and Polarization

PANEL CUTOUT DIMENSIONS

Jam-Nut Panel Cutout Dimensions		
Shell Size	A Flat ± .002 (.05)	Ø B
5	.355 (9.02)	.385 (9.78) .380 (9.65)
6	.415 (10.54)	.447 (11.35) .442 (11.23)
7	.541 (13.74)	.577 (14.66) .567 (14.40)
8	.601 (15.27)	.635 (16.13) .630 (16.00)
9	.601 (15.27)	.635 (16.13) .630 (16.00)
10	.729 (18.52)	.760 (19.30) .755 (19.18)
12	.850 (21.59)	.885 (22.48) .880 (22.35)
14	1.031 (26.19)	1.072 (27.23) 1.067 (27.10)

Flange Mount Panel Cutout Dimensions		
Shell Size	A	Ø B
5	.513 (13.03)	.382 (9.70)
6	.598 (15.19)	.445 (11.30)
7	.708 (17.98)	.520 (13.21)
8	.964 (24.49)	.592 (15.04)
9	1.017 (25.83)	.645 (16.38)
10	1.101 (27.97)	.726 (18.44)
12	1.204 (30.58)	.832 (21.13)
14	1.280 (32.51)	.950 (24.13)

POLARIZATION

Plug Keyway Polarization		
Pos.	A°	B°
N	150°	210°
X	75°	210°
Y	95°	230°
Z	140°	275°

Receptacle Keyway Polarization		
Pos.	A°	B°
N	150°	210°
X	75°	210°
Y	95°	230°
Z	140°	275°

SERIES 803 BAYONET-LOCK