Glenair®

600H005
Connector Holding Tool
MIL-DTL-38999 Series III
Plug and Receptacle

Product Series	Basic Number		Shell Size	Contact Style	Polarization
600	H	005 -	17	P	N

- **Product Series:** 600
- **Basic Number:** H — D38999 Series III Holding Tool Connector Code
- **Basic Number:** 005 -
- **Shell Size:** 17
- **Contact Style:** P - *Plug Holder*; R - *Receptacle Holder*
- **Polarization:** P, N — *A, B, C, D or E (N = Normal)*



Receptacle Holder

Plug Holder

Connector Shell Size	MIN/MAX IN-LB			A Dia Max	B Dia Max	C Dim Max
	Aluminum	Composite	Stainless Steel High Vibration Applications			
09, A	51/61	20/25	91/101	.577 (14.7)	.438 (11.1)	1.031 (26.2)
11, B	71/81	20/30	115/125	.709 (18.0)	.566 (14.4)	1.031 (26.2)
13, C	03/113	25/35	115/125	.829 (21.1)	.678 (17.2)	1.031 (26.2)
15, D	111/121	25/35	139/149	.954 (24.2)	.803 (20.4)	1.031 (26.2)
17, E	111/121	30/40	139/149	1.107 (28.1)	.928 (23.6)	1.031 (26.2)
19, F	111/121	30/40	175/185	1.190 (30.2)	1.033 (26.2)	1.031 (26.2)
21, G	131/141	35/45	199/209	1.315 (33.4)	1.158 (29.4)	1.031 (26.2)
23, H	131/141	35/45	223/233	1.440 (36.6)	1.283 (32.6)	1.031 (26.2)
25, J	131/141	35/45	259/269	1.565 (39.8)	1.408 (35.8)	1.031 (26.2)

NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 09, 11 and 13; 3/8" - Shell sizes 15 and up.
4. Composite values apply when using Glenair 600-091 and 600-007 tools.

© 2010 Glenair, Inc. MIL-DTL-38999 Cylindrical Connectors CAGE CODE 06324 Printed in U.S.A.